

## SBG34HF010KG/US



|                    |         |                           |
|--------------------|---------|---------------------------|
| Measuring range    | [l/min] | 4...100                   |
| Process connection |         | threaded connection G 3/4 |

|                    |       |                                            |
|--------------------|-------|--------------------------------------------|
| Media              |       | Liquids; water; glycol solutions; coolants |
| Medium temperature | [°C]  | -10...100                                  |
| Pressure rating    | [bar] | 25                                         |
| Pressure rating    | [MPa] | 2.5                                        |

|                     |      |                            |
|---------------------|------|----------------------------|
| Operating voltage   | [V]  | 18...32 DC; (to SELV/PELV) |
| Current consumption | [mA] | < 35                       |
| Protection class    |      | III                        |



## Flow transmitter with integrated backflow prevention

SBG34HF010KG/US

|                                |                                                                                             |
|--------------------------------|---------------------------------------------------------------------------------------------|
| Reverse polarity protection    | yes                                                                                         |
| <b>Outputs</b>                 |                                                                                             |
| Output signal                  | analogue signal                                                                             |
| Analogue current output [mA]   | 4...20                                                                                      |
| Max. load [Ω]                  | 500                                                                                         |
| Short-circuit protection       | yes                                                                                         |
| Overload protection            | yes                                                                                         |
| <b>Measuring/setting range</b> |                                                                                             |
| Measuring range [l/min]        | 4...100                                                                                     |
| <b>Accuracy / deviations</b>   |                                                                                             |
| Repeatability [X16]            | 1                                                                                           |
| Measuring error [X16]          | ± 5                                                                                         |
| <b>Response times</b>          |                                                                                             |
| Response time [s]              | < 0.01                                                                                      |
| <b>Operating conditions</b>    |                                                                                             |
| Ambient temperature [°C]       | 0...60                                                                                      |
| Storage temperature [°C]       | -15...80                                                                                    |
| Protection                     | IP 65; IP 67                                                                                |
| <b>Tests / approvals</b>       |                                                                                             |
| EMC                            | DIN EN 61000-6-2                                                                            |
|                                | DIN EN 61000-6-3                                                                            |
| Shock resistance               | DIN EN 60068-2-27                                                                           |
| Vibration resistance           | DIN EN 60068-2-6                                                                            |
| MTTF [ANN]                     | 778                                                                                         |
| <b>Mechanical data</b>         |                                                                                             |
| Weight [g]                     | 1297.6                                                                                      |
| Materials                      | brass chemically nickel-plated; PP; stainless steel (1.4404 / 316L); aluminium anodised; PA |
| Materials (wetted parts)       | stainless steel (316 / 1.4401); brass; brass chemically nickel-plated; PP; PPS; O-ring: FKM |
| Process connection             | threaded connection G 3/4                                                                   |
| Switching cycles mechanical    | 10 million                                                                                  |
| <b>Remarks</b>                 |                                                                                             |
| Remarks                        | Recommendation Use 200 micron filtration                                                    |
|                                | All data refer to water (20 °C).                                                            |
| Notes                          | Please note the changed housing design!                                                     |
| Pack quantity                  | 1 pcs.                                                                                      |

## Flow transmitter with integrated backflow prevention

SBG34HF010KG/US

### Electrical connection

Connector: 1 x M12; coding: A



### Connection




colours to DIN EN 60947-5-2

Core colours :

BN = brown  
BU = blue  
WH = white

### Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity