

SBG34IF0FRKG

Please note the changed housing design!



Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
Measuring range	2...100 l/min	0.12...6 m³/h
Process connection	threaded connection G 3/4	

Special feature	Gold-plated contacts
Application	for industrial applications
Media	Liquids; water; glycol solutions; coolants



Flow meter with integrated backflow prevention and display

SBG34IF0FRKG

Note on media		oil 1 with viscosity: 10 mm ² /s (40 °C)
		oil 2 with viscosity: 46 mm ² /s (40 °C)
Medium temperature	[°C]	-10...100
Pressure rating	[bar]	25
Pressure rating	[MPa]	2.5
MAWP (for applications according to CRN)	[bar]	25
Electrical data		
Operating voltage	[V]	18...30 DC; (to SELV/PELV)
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	< 3
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1
Outputs		
Total number of outputs		2
Output signal		switching signal; analogue signal; frequency signal; IO-Link; (configurable)
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	150; (per output 2 x 200 (...60 °C); 2 x 250 (...40 °C))
Switching cycles (mechanical)		10 million
Number of analogue outputs		1
Analogue current output	[mA]	4...20
Max. load	[Ω]	500
Short-circuit protection		yes
Overload protection		yes
Frequency of the output	[Hz]	0...10000
Measuring/setting range		
Measuring range		2...100 l/min 0.12...6 m ³ /h
Display range		0...120 l/min 0...7.2 m ³ /h
Resolution		0.5 l/min 0.05 m ³ /h
Set point SP		1...100 l/min 0.05...6 m ³ /h
Reset point rP		0...99 l/min 0...5.95 m ³ /h
Frequency end point, FEP		6.5...100 l/min 0.4...6 m ³ /h
In steps of		0.5 l/min 0.05 m ³ /h
Frequency at the end point FRP	[Hz]	10...10000
Measuring dynamics		1:50
Temperature monitoring		
Measuring range	[°C]	-10...100
Display range	[°C]	-32...122



Flow meter with integrated backflow prevention and display

SBG34IF0FRKG

Resolution	[°C]	1
Set point SP	[°C]	-9...100
Reset point rP	[°C]	-10...99
In steps of	[°C]	1
Frequency start point, FSP	[°C]	-10...78
Frequency end point, FEP	[°C]	12...100
Frequency at the end point FRP	[Hz]	10...10000

Accuracy / deviations

Flow monitoring

Accuracy (in the measuring range)	$\pm (4 \% MW + 1 \% MEW)$; ($Q > 2 \text{ l/min}$; medium and operating temperature: $+22 \text{ °C} \pm 4 \text{ K}$)
Repeatability	$\pm 1 \% MEW$

Temperature monitoring

Temperature drift	0,029 °C / K
Accuracy [K]	3 K (25°C; $Q > 1 \text{ l/min}$)

Response times

Flow monitoring

Response time [s]	0.01
Damping process value dAP [s]	0...5
Damping for the analogue output dAA [s]	0...5

Temperature monitoring

Dynamic response T05 / T09 [s]	T09 = 120 ($Q > 1 \text{ l/min}$)
--------------------------------	-------------------------------------

Software / programming

Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; current/frequency output; medium selection; damping for the switching output / analogue output; display can be rotated and switched off; standard unit of measurement; process value colour
---------------------------	--

Interfaces

Communication interface	IO-Link				
Transmission type	COM2 (38,4 kBaud)				
IO-Link revision	1.1				
SDCI standard	IEC 61131-9 CDV				
Profiles	Smart Sensor: Process Data Variable; Device Identification				
SIO mode	yes				
Required master port type	A				
Process data analogue	2				
Process data binary	2				
Min. process cycle time [ms]	5				
Supported DeviceIDs	<table> <tr> <th>Type of operation</th><th>DeviceID</th></tr> <tr> <td>default</td><td>563</td></tr> </table>	Type of operation	DeviceID	default	563
Type of operation	DeviceID				
default	563				

Operating conditions

Ambient temperature [°C]	0...60
Note on ambient temperature	medium temperature < 80 °C medium temperature < 100 °C: 0...40 °C



Flow meter with integrated backflow prevention and display

SBG34IF0FRKG

Storage temperature	[°C]	-15...80
Protection		IP 65; IP 67

Tests / approvals

EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[ANN]	145
UL approval	UL Approval no.	I006
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data

Weight	[g]	1488.75
Materials	stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated	
Materials (wetted parts)	stainless steel (316 / 1.4401); stainless steel (1.4404 / 316L); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM	
Process connection	threaded connection G 3/4	

Displays / operating elements

Display	Display unit	3 x LED, green
	switching status	2 x LED, yellow
	measured values	alphanumeric display, red/green 4-digit
	programming	alphanumeric display, 4-digit

Remarks

Remarks	Recommendation: use a 200-micron filter.
	All data refer to water (20 °C).
	MW = measured value
	MEW = Final value of the measuring range
Notes	Please note the changed housing design!
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated





Flow meter with integrated backflow prevention and display

SBG34IF0FRKG

Connection



OUT1:

- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- frequency output volumetric flow quantity monitoring
- frequency output Temperature monitoring
- IO-Link

OUT2:


- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- analogue output volumetric flow quantity monitoring
- analogue output Temperature monitoring
- colours to DIN EN 60947-5-2

Core colours :

BK = black
BN = brown
BU = blue
WH = white

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity