
SD6500

Compressed air meter

SDR12DGXFRKG/US-100



Product characteristics			
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1	
Measuring range	4...1250 l/min	0.3...99.8 m/s	0.25...75 m³/h
Process connection		threaded connection R 1/2 DN15	
Application			
Application		for industrial applications	
Media		compressed air	
Medium temperature	[°C]	-10...60	
Min. bursting pressure	[bar]	64	
Min. bursting pressure	[MPa]	6.4	
Pressure rating	[bar]	16	
Pressure rating	[MPa]	1.6	
MAWP (for applications according to CRN)	[bar]	9.7	
Electrical data			
Operating voltage	[V]	18...30 DC; (to SELV/PELV)	

SD6500

Compressed air meter

SDR12DGXFRKG/US-100

Current consumption	[mA]	< 80
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	1
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1
Inputs		
Inputs		counter reset
Outputs		
Output signal		switching signal; analogue signal; pulse signal; IO-Link; (configurable)
Electrical design		PNP/NPN
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	150; (per output)
Number of analogue outputs		1
Analogue current output	[mA]	4...20; (scalable)
Max. load	[Ω]	500
Pulse output		consumed quantity meter
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Measuring/setting range			
Measuring range	4...1250 l/min	0.3...99.8 m/s	0.25...75 m³/h
Display range	0...1500 l/min	0...119.8 m/s	0...90 m³/h
Resolution	1 l/min	0.1 m/s	0.05 m³/h
Set point SP	11...1250 l/min	0.9...99.8 m/s	0.65...74.97 m³/h
Reset point rP	5...1243 l/min	0.4...99.3 m/s	0.28...74.6 m³/h
Analogue start point ASP	0...1000 l/min	0...79.8 m/s	0...60 m³/h
Analogue end point AEP	250...1250 l/min	20...99.8 m/s	15...75 m³/h
Low flow cut-off LFC	1...13 l/min	0.1...1.1 m/s	0.09...0.8 m³/h
In steps of	1 l/min	0.1 m/s	0.01 m³/h

Pressure monitoring		
Measuring range	[bar]	-1...16
Display range	[bar]	-1...20
Resolution	[bar]	0.05
Set point SP	[bar]	-0.92...16
Reset point rP	[bar]	-1...15.92
Analogue start point	[bar]	-1...12.8
Analogue end point	[bar]	2.2...16
In steps of	[bar]	0.01

SD6500

Compressed air meter

SDR12DGXFRKG/US-100

Volumetric flow quantity monitoring			
Measuring range		0...100000000 m³	0...353146667.2 scf
Display range		0...100000000 m³	0...353146667.2 scf
Set point SP		0.001...10000000 m³	0.05...353146667.2 scf
Pulse value		0.001...10000000 m³	0.05...353146667.2 scf
In steps of		0.0001 m³	0.005 scf
Pulse length	[s]	0.002...2	
Temperature monitoring			
Measuring range		-10...60 °C	14...140 °F
Display range		-24...74 °C	-11.2...165.2 °F
Resolution		0.2 °C	0.5 °F
Set point SP		-9.7...60 °C	14.6...140 °F
Reset point rP		-10...59.7 °C	14...139.4 °F
Analogue start point		-10...46 °C	14...114.8 °F
Analogue end point		4...60 °C	39.2...140 °F
In steps of		0.1 °C	0.1 °F
Accuracy / deviations			
Temperature coefficient	[1/K]	± 0,07 % MW	
Accuracy (in the measuring range)		class 141: ± (2 % MW + 0,5 % MEW); class 344: ± (6 % MW + 0,6 % MEW) ; air quality to ISO 8573-1:2010; at medium temperature 23 °C	
Repeatability		± (0,4 % MW + 0,1 % MEW)	
Pressure monitoring			
Repeatability	[X16]	± 0,2	
Characteristics deviation	[X16]	< ± 0,5; (BFSL = Best Fit Straight Line)	
Greatest TEMPCO of the span	[% MEW / 10 K]	± 0,3	
Greatest TEMPCO of the zero point	[% MEW / 10 K]	± 0,1	
Temperature monitoring			
Accuracy	[K]	± 0,5; (medium flow in the limit area of the flow measurement range)	
Response times			
Response time	[s]	0.1; (dAP = 0)	
Damping process value dAP	[s]	0...5	
Pressure monitoring			
Response time	[s]	0.05	
Temperature monitoring			
Dynamic response T05 / T09	[s]	T09 = 0,5	
Software / programming			
Parameter setting options		hysteresis / window; normally open / normally closed; current/pulse output; display can be rotated and switched off; Display unit; totaliser	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	

SD6500

Compressed air meter

SDR12DGXFRKG/US-100

SDCI standard		IEC 61131-9 CDV	
Profiles		Digital Measuring Sensor (0x800A), Identification and Diagnosis (0x4000)	
SIO mode		yes	
Required master port type		A	
Process data analogue		8	
Process data binary		2	
Min. process cycle time	[ms]	7.2	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	862
Operating conditions			
Ambient temperature	[°C]	0...60	
Storage temperature	[°C]	-20...85	
Max. relative air humidity	[%]	90	
Protection		IP 65; IP 67	
Tests / approvals			
EMC		DIN EN 60947-5-9	
CPA approval		model number	001TG
		accuracy class	-
		maximum allowable error	± 2,5 % FS
		Q (min)	0,25 m³/h
		Q (t)	-
		Q (max)	75 m³/h
Vibration resistance		DIN EN 68000-2-6	5 g (10...2000 Hz)
MTTF	[ANN]	183	
UL approval		UL Approval no.	I012
		File number UL	E174189
Pressure Equipment Directive		Sound engineering practice; can be used for stable gases fluid group 2	
Mechanical data			
Weight	[g]	728.5	
Materials		PBT+PC-GF30; PPS GF40; stainless steel (1.4301 / 304); stainless steel (1.4305 / 303); steel (1.5523) galvanised; 2.0401 (brass / CW614N); FKM	
Materials (wetted parts)		stainless steel (1.4301 / 304); stainless steel (1.4305 / 303); FKM; ceramics glass passivated; PPS GF40; Al2O3 (ceramics); acrylate	
Process connection		threaded connection R 1/2 DN15	
Displays / operating elements			
Display			colour display 1,44", 128 x 128 pixels
			2 x LED, yellow
Remarks			
Remarks		MW = measured value	
		MEW = Final value of the measuring range	
		Measuring, display and setting ranges refer to the standard volume flow according to DIN ISO 2533.	
		For information about installation and operation please see the operating instructions.	
Pack quantity		1 pcs.	


SD6500

Compressed air meter


SDR12DGXFRKG/US-100

Electrical connection

Connector: 1 x M12; coding: A



Connection



OUT1/IO-Link:	switching output flow switching output temperature switching output pressure Pulse output quantity meter signal output Preset counter
OUT2/InD:	switching output flow switching output temperature switching output pressure analogue output flow analogue output temperature analogue output pressure signal output Preset counter Pulse output quantity meter input counter reset