

SD6100




Flow rate meter for gases

SDR12DGXFPKG/US-100

phase-out article
Discontinuation date: 12/31/2024

Alternative articles: SD6600
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1
Process connection		
		threaded connection R 1/2 DN15
Ar		
Measuring range	[m³/h]	0.4...122
CO2		
Measuring range	[m³/h]	0.2...74.7
N2		
Measuring range	[m³/h]	0.2...75
Application		
Application		for industrial applications
Media		Argon (Ar); carbon dioxide (CO2); nitrogen (N2)
Medium temperature	[°C]	0...60
Pressure rating	[bar]	16
Pressure rating	[MPa]	1.6
Electrical data		
Operating voltage	[V]	18...30 DC; (to SELV/PELV)
Current consumption	[mA]	< 100



Flow rate meter for gases

SDR12DGXFPKG/US-100

Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	1

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
------------------------------	---

Outputs

Total number of outputs	2
Output signal	switching signal; analogue signal; pulse signal; IO-Link; (configurable)
Electrical design	PNP
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	250; (per output)
Number of analogue outputs	1
Analogue current output [mA]	4...20; (scalable)
Max. load [Ω]	500
Pulse output	consumed quantity meter
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Measuring/setting range

Low flow cut-off LFC [m³/h]	< 1.3
Measuring dynamics	1:300

Ar	
Measuring range [m³/h]	0.4...122
Display range [m³/h]	0...146.4
Resolution [m³/h]	0.1
Set point SP [m³/h]	1.1...122
Reset point rP [m³/h]	0.6...121.5
Analogue start point ASP [m³/h]	0...97.6
Analogue end point AEP [m³/h]	24.4...122
In steps of [m³/h]	0.1

CO2	
Measuring range [m³/h]	0.2...74.7
Display range [m³/h]	0...89.7
Resolution [m³/h]	0.1
Set point SP [m³/h]	0.7...74.7
Reset point rP [m³/h]	0.4...74.4
Analogue start point ASP [m³/h]	0...59.8
Analogue end point AEP [m³/h]	14.9...74.7
In steps of [m³/h]	0.1



Flow rate meter for gases

SDR12DGXFPKG/US-100

Volumetric flow quantity monitoring		
Pulse value		0.001...1 000 000 m ³
In steps of		0.001...1000 m ³
Pulse length	[s]	0,012...2
N2		
Measuring range	[m ³ /h]	0.2...75
Display range	[m ³ /h]	0...90
Resolution	[m ³ /h]	0.1
Set point SP	[m ³ /h]	0.7...75
Reset point rP	[m ³ /h]	0.4...74.7
Analogue start point ASP	[m ³ /h]	0...60
Analogue end point AEP	[m ³ /h]	15...75
In steps of	[m ³ /h]	0.1
Temperature monitoring		
Measuring range	[°C]	0...60
Display range	[°C]	-12...72
Resolution	[°C]	0.2
Set point SP	[°C]	0.4...60
Reset point rP	[°C]	0...59.8
Analogue start point	[°C]	0...48
Analogue end point	[°C]	12...60
In steps of	[°C]	0.2
Accuracy / deviations		
Flow monitoring		
Repeatability	[X17]	± 1,5
Accuracy (in the measuring range)		± (6 % MW + 0,6 % MEW); (conditions: installation to DIN ISO 2533; installation in pipes: DN15)
Temperature monitoring		
Accuracy	[K]	± 2; (medium flow in the limit area of the flow measurement range)
Response times		
Flow monitoring		
Response time	[s]	0.1; (dAP = 0)
Damping process value dAP in steps	[s]	0 - 0,2 - 0,4 - 0,6 - 0,8 - 1
Software / programming		
Parameter setting options		Flow monitoring; quantity meter; Preset counter; hysteresis / window; normally open / normally closed; current/pulse output; display can be rotated and switched off; Display unit; medium selection
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9
Profiles		Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis

SD6100



Flow rate meter for gases

SDR12DGXFPKG/US-100

SIO mode	yes	
Required master port type	A	
Process data analogue	3	
Process data binary	2	
Min. process cycle time [ms]	4.1	
Supported DeviceIDs	Type of operation	DeviceID
	default	265

Operating conditions		
Ambient temperature [°C]		0...60
Storage temperature [°C]		-20...85
Max. relative air humidity [%]		90
Protection		IP 65

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
CPA approval	model number	003TG
	accuracy class	-
	maximum allowable error	± 7 % FS
	Q (min)	0,2 m³/h (N2)
		0,2 m³/h (CO2)
		0,4 m³/h (Ar)
	Q (t)	-
	Q (max)	75 m³/h (N2)
		74,7 m³/h (CO2)
		122 m³/h (Ar)
Vibration resistance	DIN IEC 68-2-6	5 g (55...2000 Hz)
MTTF [ANN]		227
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight [g]		963.5
Materials	PBT-GF20; PC; PC; stainless steel (1.4301 / 304); FKM	
Materials (wetted parts)	stainless steel (1.4301 / 304); ceramics glass passivated; PEEK; polyester; FKM; aluminium anodised	
Tightening torque [Nm]		50
Process connection	threaded connection R 1/2 DN15	

Displays / operating elements		
Display	Display unit	4 x LED, green (NI/min, Nm³/h, Nm³, °C)
	function display	1 x LED, yellow
	switching status	2 x LED, yellow
	measured values	alphanumeric display, 4-digit
	programming	alphanumeric display, 4-digit
Display unit	NI/min; Nm³/h; Nm³; °C	

SD6100



Flow rate meter for gases

SDR12DGXFPKG/US-100



Remarks	
Remarks	MW = measured value
	MEW = Final value of the measuring range
	Measuring, display and setting ranges refer to the standard volume flow according to DIN ISO 2533.
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection



OUT1:	switching output Pulse output quantity meter signal output Preset counter
OUT2:	switching output analogue output