

SF3000




Flow sensor for connection to an evaluation unit

SFR12ABA

Article no longer available - archive entry

Alternative articles: SF5350 + E40096

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Process connection	G 1/2 external thread
--------------------	-----------------------

Application

Application	high-temperature range
Media	Liquids; Gases
Medium temperature	[-25...80
Pressure rating	30

Liquids

Application	high-temperature range
Medium temperature	[-25...80

Gases

Medium temperature	[-25...80
--------------------	-----------

Electrical data

Connection to control monitor	VS 0200
-------------------------------	---------

Measuring/setting range

Liquids

Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60

Gases

Setting range	[cm/s]	200...2000
Greatest sensitivity	[cm/s]	200...800

Accuracy / deviations

Temperature gradient	[K/min]	15
----------------------	---------	----

Response times

Response time	[s]	1...10
---------------	-----	--------

Liquids

Response time	[s]	1...10
---------------	-----	--------


SF3000



Flow sensor for connection to an evaluation unit

SFR12ABA

Gases	
Response time	[s] 1...10
Operating conditions	
Protection	IP 67
Mechanical data	
Housing	threaded type
Materials	stainless steel (1.4305 / 303)
Materials (wetted parts)	stainless steel (1.4305 / 303)
Process connection	G 1/2 external thread
Аксессуары	
Items supplied	sealings: 2 x AMF 30
Remarks	
Pack quantity	1 pcs.
Electrical connection	
Cable: 2 m, PUR; Maximum cable length: 100 m; 5 x 0.34 mm ² , PVC	
Connection	



	Core colours :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey