




Pressure switch with IO-Link

PV-025MSER14-UFRVG/US/ /



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2
Measuring range [MPa]	-0.1...2.5
Process connection	threaded connection R 1/4 external thread internal thread:M5

Application

Measuring element	metallic thin film cell
Application	for industrial applications
Media	liquids and gases
Medium temperature [°C]	-40...90
Min. bursting pressure [MPa]	60
Pressure rating [MPa]	6.5
Note on pressure rating	static
Vacuum resistance [mbar]	-1000
Type of pressure	relative pressure

Electrical data

Operating voltage [V]	18...30 DC
Current consumption [mA]	< 15
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	< 0.3

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2
------------------------------	------------------------------

Outputs

Total number of outputs	2
Output signal	switching signal; IO-Link; (configurable)
Electrical design	PNP/NPN
Number of digital outputs	2



Pressure switch with IO-Link

PV-025MSER14-UFRVG/US/ /

Output function	normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC [V]	2		
Permanent current rating of switching output DC [mA]	100		
Switching frequency DC [Hz]	< 170		
Short-circuit protection	yes		
Type of short-circuit protection	pulsed		
Overload protection	yes		

Measuring/setting range			
Measuring range [MPa]	-0.1...2.5		
Set point SP [MPa]	-0.075...2.5		
Reset point rP [MPa]	-0.087...2.488		
In steps of [MPa]	0.001		
Factory setting	SP1 = 0.625 MPa	rP1 = 0.575 MPa	ou1 = Hno;
	SP2 = 1.875 MPa	rP2 = 1.825 MPa	ou2 = Hno;
	dS1/dS2 = 0 ms	dr1/dr2 = 0 ms	
	coF = 0 %	P-n = PnP	dAP= 60 ms

Accuracy / deviations	
Switch point accuracy [X21]	< ± 0,5 (nach DIN EN 61298-2)
Repeatability [X21]	< ± 0,05; (with temperature fluctuations < 10 K)
Characteristics deviation [X21]	< ± 0,5; (linearity incl. hysteresis and repeatability, limit value setting to DIN EN IEC 62828-1)
Linearity deviation [X21]	< ± 0,1 (BFSL) / < ± 0,2 (LS)
Hysteresis deviation [X21]	< ± 0,2
Long-term stability [X21]	< ± 0,1; (per 6 months)
Temperature coefficient zero point [X22]	< 0,1 (-25...90 °C) / < 0,2 (-40...-25 °C)
Temperature coefficient span [X22]	< 0,1 (-25...90 °C) / < 0,2 (-40...-25 °C)

Response times	
Response time [ms]	< 3

Software / programming	
Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; switch-on/switch-off delay; Damping

Interfaces	
Communication interface	IO-Link
Transmission type	COM2 (38,4 kBaud)
IO-Link revision	1.1
SDCI standard	IEC 61131-9
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis
SIO mode	yes
Required master port type	A
Process data analogue	2
Process data binary	2
Min. process cycle time [ms]	5

PV7703



Pressure switch with IO-Link

PV-025MSER14-UFRVG/US/ /

Supported DeviceIDs	Type of operation	DeviceID
	default	783

Operating conditions		
Ambient temperature	[°C]	-40...90
Storage temperature	[°C]	-40...100
Protection		IP 67; IP 69K

Tests / approvals		
EMC	DIN EN 61326-1	
Shock resistance	DIN EN 60068-2-27	500 g (1 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[ANN]	667.77
UL approval	UL Approval no.	J015
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight	[g]	63
Materials	1.4542 (17-4 PH / 630); stainless steel (1.4404 / 316L); PEI	
Materials (wetted parts)	stainless steel (1.4305 / 303); 1.4542 (17-4 PH / 630)	
Min. pressure cycles	60 million; (at 1.2 times nominal pressure)	
Tightening torque	[Nm]	50; (recommended tightening torque; depends on lubrication, seal and pressure rating)
Process connection	threaded connection R 1/4 external thread internal thread:M5	
Restrictor element integrated	yes	

Remarks		
Remarks	BFSL = Best Fit Straight Line	
	LS = limit value setting	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A




PV7703



Pressure switch with IO-Link

PV-025MSER14-UFRVG/US/ /

Connection



OUT1	switching output
	IO-Link
OUT2	switching output
	colours to DIN EN 60947-5-2
	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white