


SM0100



Control monitor for flow sensors

VS0200/ 90-265VAC/DC

Article no longer available - archive entry



1 mounting on DIN rail



Application		
Application		Flow monitoring
Electrical data		
Operating voltage	[V]	90...265 AC/DC
Power-on delay time	[s]	30
Number of channels		1
Outputs		
Electrical design		relay
Contact rating		4 A, 250 V AC
Switching function flow monitoring		relay energised when flow is present
Software / programming		
Adjustment of the switch point		potentiometer
Selection liquids / gases		slide switch
Operating conditions		
Ambient temperature	[°C]	0...60
Protection		IP 40
Protection rating terminals		IP 20
Mechanical data		
Housing		housing for DIN rail mounting
Dimensions	[mm]	75 x 55 x 110
Materials		plastics

SM0100



Control monitor for flow sensors

VS0200/ 90-265VAC/DC

Displays / operating elements

Display	function	11 x LED
---------	----------	----------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

terminals: 16 x ...2.5 mm²

Connection



- 1: Relais Flow monitoring
Core colours :
BN = brown
BU = blue
BK = black
WH = white
GY = grey