




Pressure sensor with display

PN-025-RDR12-MFRKG/US/ IV



Product characteristics			
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Measuring range	-1...25 bar	-14.5...362.5 psi	-0.1...2.5 MPa
Process connection	threaded connection G 1/2 external thread		
Application			
Special feature	Gold-plated contacts		
Application	встановлення врівень для промислового застосування; for industrial applications		
Media	liquids and gases		
Medium temperature [°C]	-20...125		
Min. bursting pressure	200 bar	2900 psi	20 MPa
Pressure rating	100 bar	1450 psi	10 Mpa
Type of pressure	relative pressure		
No dead space	yes		
Electrical data			
Operating voltage [V]	18...32 DC; (to SELV/PELV)		
Current consumption [mA]	< 35		
Min. insulation resistance [MΩ]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		



Pressure sensor with display

PN-025-RDR12-MFRKG/US/ /V

Power-on delay time	[s]	0.3
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
------------------------------	---

Outputs

Total number of outputs	2
Output signal	switching signal; analogue signal; (configurable)
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V] 2
Permanent current rating of switching output DC	[mA] 250
Switching frequency DC	[Hz] < 500
Number of analogue outputs	1
Analogue current output	[mA] 4...20; (scalable 1:4)
Max. load	[Ω] (U _b - 10 V) / 20 mA
Analogue voltage output	[V] 0...10; (scalable 1:4)
Min. load resistance	[Ω] 2000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Measuring/setting range

Measuring range	-1...25 bar	-14.5...362.5 psi	-0.1...2.5 MPa
Set point SP	-0.8...25 bar	-11.5...362.5 psi	-0.08...2.5 MPa
Reset point rP	-0.9...24.9 bar	-13...361 psi	-0.09...2.49 MPa
Analogue start point	-1...18.75 bar	-14.5...272 psi	-0.1...1.88 MPa
Analogue end point	5.25...25 bar	76...362.5 psi	0.53...2.5 MPa
In steps of	0.05 bar	0.5 psi	0.01 MPa
Factory setting		SP1 = 6.25 bar	rP1 = 5.75 bar
		SP2 = 18.75 bar	rP2 = 18.25 bar
		ASP = 0.00 bar	AEP = 25.00 bar

Accuracy / deviations

Switch point accuracy	[X21]	< ± 0,4; (Turn down 1:1)
Repeatability	[X21]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)
Characteristics deviation	[X21]	< ± 0,3 (BFSL) / < ± 0,6 (LS); (Turn down 1:1; BFSL = Best Fit Straight Line; LS = limit value setting)
Linearity deviation	[X21]	< ± 0,5; (Turn down 1:1)
Hysteresis deviation	[X21]	< ± 0,1; (Turn down 1:1)
Long-term stability	[X21]	< ± 0,1; (Turn down 1:1; per year)
Temperature coefficient zero point	[X22]	< ± 0,25; (0...80 °C)
Temperature coefficient span	[X22]	< ± 0,25; (0...80 °C)



Pressure sensor with display

PN-025-RDR12-MFRKG/US/ IV

Response times		
Response time	[ms]	< 1.5
Damping process value dAP	[s]	0.01...4
Damping for the analogue output dAA	[s]	0.01...4
Max. response time analogue output	[ms]	3
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; current/voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; zero point; span	
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 65
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[ANN]	167.14
Mechanical data		
Weight	[g]	390
Materials	stainless steel (1.4301 / 304); stainless steel (1.4435 / 316L); PC; PBT; PEI; PTFE	
Materials (wetted parts)	stainless steel (1.4435 / 316L)	
Min. pressure cycles	10 million	
Process connection	threaded connection G 1/2 external thread	
Fill fluid for pressure transfer	NEOBEE (food grade, FDA compliant)	
Displays / operating elements		
Display	Display unit	3 x LED, green
	switching status	2 x LED, yellow
	function display	alphanumeric display, 4-digit
	measured values	alphanumeric display, 4-digit
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x M12; coding: A; Contacts: gold-plated		
		



Pressure sensor with display

PN-025-RDR12-MFRKG/US/ IV

Connection



OUT1	switching output
OUT2	switching output
	analogue output
	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white