


# SM9604



## Magnetic-inductive flow meter

SMN32XGX50KG/US-100



| Product characteristics      |                                                   |               |               |                |
|------------------------------|---------------------------------------------------|---------------|---------------|----------------|
| Number of inputs and outputs | Number of analogue outputs: 2                     |               |               |                |
| Measuring range              | 5...300 l/min                                     | 0.3...18 m³/h | 80...4755 gph | 1.3...79.3 gpm |
| Process connection           | threaded connection 1 1/2" NPT DN40               |               |               |                |
| Application                  |                                                   |               |               |                |
| Special feature              | Gold-plated contacts                              |               |               |                |
| Application                  | empty pipe detection; for industrial applications |               |               |                |
| Media                        | conductive liquids; water; hydrous media          |               |               |                |
| Note on media                | conductivity: ≥ 20 µS/cm                          |               |               |                |
|                              | viscosity: < 70 mm²/s (40 °C)                     |               |               |                |



## Magnetic-inductive flow meter

SMN32XGX50KG/US-100

|                                                |             |             |
|------------------------------------------------|-------------|-------------|
| Medium temperature                             | -10...90 °C | 14...194 °F |
| Pressure rating [bar]                          | 16          |             |
| Pressure rating [MPa]                          | 1.6         |             |
| Pressure rating [psi]                          | 232         |             |
| MAWP (for applications according to CRN) [bar] | 16          |             |

## Electrical data

|                             |                            |
|-----------------------------|----------------------------|
| Operating voltage [V]       | 18...32 DC; (to SELV/PELV) |
| Current consumption [mA]    | < 150                      |
| Protection class            | III                        |
| Reverse polarity protection | yes                        |
| Power-on delay time [s]     | 5                          |

## Inputs / outputs

|                              |                               |
|------------------------------|-------------------------------|
| Number of inputs and outputs | Number of analogue outputs: 2 |
|------------------------------|-------------------------------|

## Outputs

|                              |                         |
|------------------------------|-------------------------|
| Total number of outputs      | 2                       |
| Output signal                | analogue signal         |
| Number of analogue outputs   | 2                       |
| Analogue current output [mA] | 4...20; ( $\leq 22$ mA) |
| Max. load [ $\Omega$ ]       | 500                     |

## Measuring/setting range

|                          |                  |                   |                  |                  |
|--------------------------|------------------|-------------------|------------------|------------------|
| Measuring range          | 5...300 l/min    | 0.3...18 m³/h     | 80...4755 gph    | 1.3...79.3 gpm   |
| Display range            | -360...360 l/min | -21.6...21.6 m³/h | -5705...5705 gph | -95.1...95.1 gpm |
| Resolution               | 0.5 l/min        | 0.02 m³/h         | 5 gph            | 0.1 gpm          |
| Analogue start point ASP | 0...240 l/min    | 0...14.4 m³/h     | 0...3800 gph     | 0...63.4 gpm     |
| Analogue end point AEP   | 60...300 l/min   | 3.6...18 m³/h     | 955...4755 gph   | 15.9...79.3 gpm  |
| Low flow cut-off LFC     | < 15 l/min       | < 0.9 m³/h        | < 240 gph        | < 4 gpm          |
| In steps of              | 0.5 l/min        | 0.02 m³/h         | 5 gph            | 0.1 gpm          |
| Measuring dynamics       | 1:60             |                   |                  |                  |

## Temperature monitoring

|                      |              |              |
|----------------------|--------------|--------------|
| Measuring range      | -20...80 °C  | -4...176 °F  |
| Display range        | -40...100 °C | -40...212 °F |
| Resolution           | 0.2 °C       | 0.5 °F       |
| Analogue start point | -20...60 °C  | -4...140 °F  |
| Analogue end point   | 0...80 °C    | 32...176 °F  |
| In steps of          | 0.2 °C       | 0.5 °F       |

## Accuracy / deviations

## Flow monitoring

|                                   |                                                |
|-----------------------------------|------------------------------------------------|
| Accuracy (in the measuring range) | $\pm (0,8 \% \text{ MW} + 0,5 \% \text{ MEW})$ |
| Repeatability                     | $\pm 0,2\% \text{ MEW}$                        |

## Temperature monitoring

|                   |                                                                                            |
|-------------------|--------------------------------------------------------------------------------------------|
| Temperature drift | $\pm 0,0333 \text{ °C / K; } \pm 0,0599 \text{ °F / K}$                                    |
| Accuracy [K]      | $\pm 1 (25 \text{ °C; } Q > 15 \text{ l/min}) / \pm 1 (77 \text{ °F; } Q > 4 \text{ gpm})$ |

# SM9604



## Magnetic-inductive flow meter

SMN32XGX50KG/US-100

| Response times                |                                                                                             |                                                |
|-------------------------------|---------------------------------------------------------------------------------------------|------------------------------------------------|
| Flow monitoring               |                                                                                             |                                                |
| Response time                 | [s]                                                                                         | 0.35; (dAP = 0)                                |
| Damping process value dAP     | [s]                                                                                         | 0...5                                          |
| Temperature monitoring        |                                                                                             |                                                |
| Dynamic response T05 / T09    | [s]                                                                                         | T09 = 3 (Q > 15 l/min) / T09 = 3 (Q > 4 gpm)   |
| Software / programming        |                                                                                             |                                                |
| Parameter setting options     | display can be deactivated; Display unit; empty pipe detection                              |                                                |
| Operating conditions          |                                                                                             |                                                |
| Ambient temperature           | -10...60 °C                                                                                 | 14...140 °F                                    |
| Storage temperature           | -25...80 °C                                                                                 | -13...176 °F                                   |
| Protection                    | IP 65; IP 67                                                                                |                                                |
| Tests / approvals             |                                                                                             |                                                |
| EMC                           | DIN EN 60947-5-9                                                                            |                                                |
|                               | DIN EN 61000-6-2                                                                            |                                                |
| CPA approval                  | model number                                                                                | 003MI                                          |
|                               | accuracy class                                                                              | -                                              |
|                               | maximum allowable error                                                                     | ± 1,5 % FS                                     |
|                               | Q (min)                                                                                     | 0,3 m³/h                                       |
|                               | Q (t)                                                                                       | -                                              |
|                               | Q (max)                                                                                     | 18 m³/h                                        |
|                               | Medium temperature                                                                          | -10...70 °C                                    |
|                               | Medium temperature                                                                          | 14...158 °F                                    |
| Shock resistance              | DIN EN 60068-2-27                                                                           | 20 g (11 ms)                                   |
| Vibration resistance          | DIN EN 60068-2-6                                                                            | 5 g (10...2000 Hz)                             |
| MTTF                          | [ANN]                                                                                       | 85                                             |
| Pressure Equipment Directive  | Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request       |                                                |
| Mechanical data               |                                                                                             |                                                |
| Weight                        | [g]                                                                                         | 2745                                           |
| Materials                     | stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti ); PEI; FKM; PBT-GF20; TPE-U |                                                |
| Materials (wetted parts)      | stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti ); PEEK; FKM                 |                                                |
| Process connection            | threaded connection 1 1/2" NPT DN40                                                         |                                                |
| Displays / operating elements |                                                                                             |                                                |
| Display                       | Display unit                                                                                | 6 x LED, green (l/min, m³/h, gpm, gph, °C, °F) |
|                               | function display                                                                            | 1 x LED, yellow (10³)                          |
|                               | measured values                                                                             | alphanumeric display, 4-digit                  |
|                               | programming                                                                                 | alphanumeric display, 4-digit                  |
| Display unit                  | l/min; m³/h; gpm; gph; °C; °F                                                               |                                                |
| Аксессуары                    |                                                                                             |                                                |
| Items supplied                | Label                                                                                       |                                                |
| Remarks                       |                                                                                             |                                                |
| Remarks                       | MW = measured value                                                                         |                                                |
|                               | MEW = Final value of the measuring range                                                    |                                                |
| Pack quantity                 | 1 pcs.                                                                                      |                                                |

# SM9604



## Magnetic-inductive flow meter

SMN32XGX50KG/US-100

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection



OUT1: colours to DIN EN 60947-5-2  
analogue output Temperature monitoring  
OUT2: analogue output volumetric flow quantity monitoring  
Core colours :  
BK = black  
BN = brown  
BU = blue  
WH = white

# SM9604




## Magnetic-inductive flow meter

SMN32XGX50KG/US-100

### Diagrams and graphs

#### Pressure loss



dP Pressure loss  
Q volumetric flow quantity