

RM3001



Absolute multiturn encoder with solid shaft

RMU Profibus

Article no longer available - archive entry

Alternative articles: RM3006

When selecting an alternative article and accessories please note that technical data may differ!



1 M4 Depth 5 mm



Product characteristics

Resolution	8192 steps; 4096 revolutions; 25 bit
Communication interface	PROFIBUS DP
Shaft design	solid shaft
Shaft diameter [mm]	6

Application

Function principle	absolute
Revolution type	multiturn

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 150
Max. revolution electrical [U/min]	6000

Outputs

Code	Dual code
------	-----------

Measuring/setting range

Resolution	8192 steps; 4096 revolutions; 25 bit
------------	--------------------------------------



Absolute multiturn encoder with solid shaft

RMU Profibus

Software / programming		
Parameter setting options		counting direction of the code values; Resolution; zero point; limit switches HI and LO; motion indicator; separation multiturn/singleturn
Diagnostic functions		
Addressing		address selector switch; 0...126
Interfaces		
Communication interface		PROFIBUS DP
PROFIBUS DP		
Transmission standard		DPV0 Class 2 (EN50170)
Transmission rate		...12 Mbit/s
Operating conditions		
Ambient temperature [°C]		-40...70
Protection		IP 66; (on the housing: IP 67; on the shaft: IP 66)
Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		10 g (55...2000 Hz)
Mechanical data		
Weight [g]		652
Dimensions [mm]		Ø 58 / L = 90.5
Materials		aluminium
Max. revolution, mechanical [U/min]		12000
Max. starting torque [Nm]		1
Reference temperature torque [°C]		20
Shaft design		solid shaft
Shaft diameter [mm]		6
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end) [N]		10
Max. shaft load radial (at the shaft end) [N]		20
Fixing flange		synchro-flange
Electrical connection		
terminal strip in the terminal chamber: ; Maximum cable length: 100 m; 400 m (1.5 Mb/s)		