


Absolute multiturn encoder with solid shaft

RMS4096-S24/LX1



M3 Depth 6 mm



Product characteristics

Resolution	4096 resolution; 8192 revolutions; 25 bit
Communication interface	SSI data interface
Shaft design	solid shaft
Shaft diameter [mm]	10

Application

Function principle	absolute
Revolution type	multiturn

Electrical data

Operating voltage [V]	4.5...30 DC
Current consumption [mA]	< 30

Inputs

Inputs	reversal of direction of rotation; reset to zero
--------	--

Outputs

Code	Gray code; (increasing code values when turned clockwise (seen on the shaft))
Code signal	Clock input; TTL-compatible signals; clock and clock (inv.) from drivers to RS 422; data output; synchronous serial; TTL-compatible signals, data, and data (inv.)

Measuring/setting range

Resolution	4096 resolution; 8192 revolutions; 25 bit
------------	---

Interfaces

Communication interface	SSI data interface
-------------------------	--------------------

Operating conditions

Ambient temperature [°C]	-25...85
Max. relative air humidity [%]	98
Protection	IP 65

Tests / approvals

Shock resistance	< 300 g (6 ms)
Vibration resistance	30 g (10...1000 Hz)
MTTF [ANN]	350



Absolute multiturn encoder with solid shaft

RMS4096-S24/LX1

Mechanical data		
Weight	[g]	247
Dimensions	[mm]	Ø 36.5 / L = 69.5
Materials		flange: aluminium; housing: steel powder-coated
Max. revolution, mechanical	[U/min]	12000
Max. starting torque	[Nm]	3
Reference temperature torque	[°C]	25
Shaft design		solid shaft
Shaft diameter	[mm]	10
Shaft material		steel
Max. shaft load axial (at the shaft end)	[N]	40
Max. shaft load radial (at the shaft end)	[N]	110
Remarks		
Remarks		Wires/pins not connected (n.c.) must not be used.
		Binder Serie 620 Connector
		79 9257 020 08 order number
Electrical connection		
Cable: 0.2 m, PUR; axial		
white	sensor 0 V	
brown	sensor Ub	
green	clock	
yellow	clock (inv.)	
grey	data	
pink	data (inv.)	
blue	reset to zero	
red	reversal of direction of rotation	
screen	housing	