


Alternative articles: SI5000 + E40101

When selecting an alternative article and accessories please note that technical data may differ!



Number of inputs and outputs	Number of digital outputs: 1
Process connection	M12 x 1

Media		Liquids
Medium temperature	[°C]	-25...80
Pressure rating	[bar]	30

Operating voltage	[V]	20...36 DC
Current consumption	[mA]	< 45
Reverse polarity protection		yes
Power-on delay time	[s]	< 20

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

Total number of outputs	1
Output signal	switching signal
Electrical design	PNP
Number of digital outputs	1

ST1609



Flow monitor

SCM12ABBFPKG/US-100-IPF

Output function	normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC [V]		2.5
Permanent current rating of switching output DC [mA]		400
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Measuring/setting range

Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60

Accuracy / deviations

Temperature gradient [K/min]	15
------------------------------	----

Response times

Response time [s]	1...10
-------------------	--------

Software / programming

Adjustment of the switch point	potentiometer
--------------------------------	---------------

Operating conditions

Ambient temperature [°C]	-20...80
Protection	IP 67

Mechanical data

Dimensions [mm]	M12 x 1
Thread designation	M12 x 1
Materials	PBT-GF20
Materials (wetted parts)	stainless steel (1.4571/316Ti)
Process connection	M12 x 1

Displays / operating elements

Display	function	11 x LED
---------	----------	----------

Аксессуары

Items supplied	sealings: 2 x AMF 30
	screwdrivers

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



ST1609



Flow monitor

SCM12ABBFPKG/US-100-IPF

Connection

