


# ST2404



## Flow sensor for connection to an evaluation unit

STR14AAC/US-100-H

Article no longer available - archive entry



### Product characteristics

Process connection	G 1/4 external thread
--------------------	-----------------------

### Application

Media	Liquids; aggressive media
-------	---------------------------

Medium temperature	[°C]	-25...80
--------------------	------	----------

Pressure rating	[bar]	5
-----------------	-------	---

### Liquids

Medium temperature	[°C]	-25...80
--------------------	------	----------

### Electrical data

Connection to control monitor	VS 0100
-------------------------------	---------

### Measuring/setting range

#### Liquids

Setting range	[cm/s]	3...300
---------------	--------	---------

Greatest sensitivity	[cm/s]	3...60
----------------------	--------	--------

### Accuracy / deviations

Temperature gradient	[K/min]	7
----------------------	---------	---

### Response times

Response time	[s]	2...20
---------------	-----	--------

#### Liquids

Response time	[s]	2...20
---------------	-----	--------

### Operating conditions

Protection	IP 67
------------	-------

### Mechanical data

Housing	threaded type
---------	---------------

# ST2404



## Flow sensor for connection to an evaluation unit

STR14AAC/US-100-H


Materials	PTFE
Process connection	G 1/4 external thread
Remarks	
Pack quantity	1 pcs.

### Electrical connection

Connector: 1 x M12; coding: A; Maximum cable length: 100 m



### Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white