


Absolute singleturn encoder with solid shaft

RMK0013-E24/E



Product characteristics

Resolution	8192 steps; 13 bit
Communication interface	PROFIBUS DP
Shaft design	solid shaft
Shaft diameter [mm]	10

Application

Function principle	absolute
Revolution type	singleturn

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	100; ((24 V))
Reverse polarity protection		yes

Outputs

Code	binary
------	--------

Measuring/setting range

Resolution	8192 steps; 13 bit
------------	--------------------

Software / programming

Parameter setting options	counting direction of the code values; Resolution; zero point; limit switches HI and LO; motion indicator; separation multiturn/singleturn
---------------------------	--



Absolute singleturn encoder with solid shaft

RMK0013-E24/E

Diagnostic functions	alarms; warnings; status; serial number of the encoder	
Addressing	address selector switch; 0...126	
Interfaces		
Communication interface	PROFIBUS DP	
PROFIBUS DP		
Transmission standard	DPV2	
Operating conditions		
Ambient temperature	[°C]	-40...85
Max. relative air humidity	[%]	98
Protection	IP 67; (on the housing: IP 67; on the shaft: IP 67)	
Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		10 g (10...2000 Hz)
MTTF	[ANN]	13
Mechanical data		
Weight	[g]	553.5
Dimensions	[mm]	Ø 58 / L = 99
Materials		aluminium
Max. revolution, mechanical [U/min]		12000
Shaft design		solid shaft
Shaft diameter	[mm]	10
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	40
Max. shaft load radial (at the shaft end)	[N]	110
Fixing flange		clamping flange
Electrical connection		
terminal strip in the terminal chamber:		