

RN7003



Absolute singleturn encoder with solid shaft

RNS0013-C24/E

Article no longer available - archive entry

Alternative articles: RN7011

When selecting an alternative article and accessories please note that technical data may differ!



1 M4 Depth 5 mm



Product characteristics

Resolution	8192 steps; 13 bit
Communication interface	CAN
Shaft design	solid shaft
Shaft diameter [mm]	6

Application

Function principle	absolute
Revolution type	singleturn

Electrical data

Operating voltage [V]	9...36 DC
Current consumption [mA]	< 250
Reverse polarity protection	yes

Outputs

Short-circuit protection	yes
Code	binary

Measuring/setting range

Resolution	8192 steps; 13 bit
------------	--------------------



Absolute singleturn encoder with solid shaft

RNS0013-C24/E

Accuracy / deviations		
Accuracy		± 1 LSB
Software / programming		
Parameter setting options		CAN parameter; scaling; preset; Baud rate; direction of rotation; address
Addressing		address selector switch; Software
Interfaces		
Communication interface		CAN
CAN		
Protocol		CANopen; DSP - 406
Operating conditions		
Ambient temperature	[°C]	-40...70
Protection		IP 66; (on the housing: IP 67; on the shaft: IP 66)
Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		10 g (55...2000 Hz)
Mechanical data		
Weight	[g]	689.2
Dimensions	[mm]	Ø 58 / L = 90.5
Materials		aluminium
Max. revolution, mechanical	[U/min]	6000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	6
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Fixing flange		synchro-flange
Electrical connection		
terminal strip in the terminal chamber: ; Maximum cable length: 25 m; 100 m (500 kb/s)		