




Control monitor for flow sensors

VS0200/110VAC

Article no longer available - archive entry

Alternative articles: SN0150
When selecting an alternative article and accessories please note that technical data may differ!



| Application | | |
|--|----------------------------------|--|
| Application | Flow monitoring; Wire monitoring | |
| Electrical data | | |
| Operating voltage tolerance | [%] | -10...10 |
| Operating voltage | [V] | < 110 AC |
| Power-on delay time | [s] | 30 |
| Number of channels | | 1 |
| Outputs | | |
| Total number of outputs | | 2 |
| Electrical design | | relay |
| Switching function flow monitoring | | relay energised when flow is present |
| Switching function wire break monitoring | | relay de-energised in case of wire break and short circuit |
| Response times | | |
| Response time | [s] | < 10 |
| Software / programming | | |
| Adjustment of the switch point | | potentiometer |
| Selection liquids / gases | | slide switch |
| Operating conditions | | |
| Ambient temperature | [°C] | 0...60 |



Control monitor for flow sensors

VS0200/110VAC

| | |
|-----------------------------|-------|
| Protection | IP 40 |
| Protection rating terminals | IP 20 |

Mechanical data

| | |
|-----------------|-------------------------------|
| Housing | housing for DIN rail mounting |
| Dimensions [mm] | 75 x 55 x 110 |
| Materials | plastics |

Displays / operating elements

| | | |
|---------|------------------|----------|
| Display | function | 11 x LED |
| | switching status | LED, red |


Remarks

| | |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

Electrical connection

terminals: 16 x ...2.5 mm²

Connection



- 1: Relais Wire monitoring
- 2: Relais Flow monitoring
- Core colours :
- BN = brown
- BU = blue
- BK = black
- WH = white
- GY = grey