

## Incremental encoder with solid shaft

RU-3000-I05/L2

Article no longer available - archive entry



- 1 reference mark
- 2 M4 Depth 5 mm



### Product characteristics

|                     |                 |
|---------------------|-----------------|
| Resolution          | 3000 resolution |
| Shaft design        | solid shaft     |
| Shaft diameter [mm] | 6               |

### Electrical data

|                                 |      |
|---------------------------------|------|
| Operating voltage tolerance [%] | 10   |
| Operating voltage [V]           | 5 DC |
| Current consumption [mA]        | 150  |

### Outputs

|                                   |     |
|-----------------------------------|-----|
| Electrical design                 | TTL |
| Max. current load per output [mA] | 20  |
| Switching frequency [kHz]         | 300 |
| Phase difference A and B [°]      | 90  |

### Measuring/setting range

|            |                 |
|------------|-----------------|
| Resolution | 3000 resolution |
|------------|-----------------|

### Operating conditions

|                                |           |
|--------------------------------|-----------|
| Ambient temperature [°C]       | -20...100 |
| Storage temperature [°C]       | -30...100 |
| Max. relative air humidity [%] | 98        |
| Protection                     | IP 64     |



## Incremental encoder with solid shaft

RU-3000-I05/L2

### Tests / approvals

|                      |                     |
|----------------------|---------------------|
| Shock resistance     | 100 g (6 ms)        |
| Vibration resistance | 10 g (55...2000 Hz) |

### Mechanical data

|                                               |                |
|-----------------------------------------------|----------------|
| Dimensions [mm]                               | Ø 58 / L = 46  |
| Materials                                     | aluminium      |
| Max. revolution, mechanical [U/min]           | 12000          |
| Max. starting torque [Nm]                     | 1              |
| Reference temperature torque [°C]             | 20             |
| Shaft design                                  | solid shaft    |
| Shaft diameter [mm]                           | 6              |
| Shaft material                                | steel (1.4104) |
| Max. shaft load axial (at the shaft end) [N]  | 10             |
| Max. shaft load radial (at the shaft end) [N] | 20             |
| Fixing flange                                 | synchro-flange |

### Electrical connection

Cable: 2 m, PUR; axial

|             |                  |
|-------------|------------------|
| brown       | A                |
| green       | A inverted       |
| grey        | B                |
| pink        | B inverted       |
| red         | 0 index          |
| black       | 0 index inverted |
| blue        | L+ sensor        |
| white       | 0V sensor        |
| brown/green | L+ (Up)          |
| white/green | 0V (Un)          |
| lilac       | failure inverted |
| screen      | housing          |

### Diagrams and graphs

|               |                                                               |
|---------------|---------------------------------------------------------------|
| Pulse diagram | <p>direction of rotation clockwise (looking at the shaft)</p> |
|---------------|---------------------------------------------------------------|