


TA2115



Temperature transmitter

TA-050CLER14-A-ZVG/US



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1
Measuring range [°C]	-50...150
Communication interface	IO-Link
Process connection	threaded connection G 1/4
Installation length EL [mm]	50

Application

Special feature	Gold-plated contacts
Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)
Media	liquids and gases
Pressure rating [bar]	400
Note on pressure rating	sensor
When mounted in adapters the specifications of the adapter data sheet apply.	

Electrical data

Operating voltage [V]	18...32 DC; ("supply class 2" to cULus)
Current consumption [mA]	< 50
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	1

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

Outputs

Total number of outputs	1
Output signal	analogue signal; IO-Link; (configurable)
Number of analogue outputs	1
Analogue current output [mA]	4...20
Max. load [Ω]	250; ((18...19 V); 19...32 V: 300 Ω)
Short-circuit protection	yes
Overload protection	yes

Measuring/setting range

Measuring range [°C]	-50...150
----------------------	-----------

TA2115



Temperature transmitter

TA-050CLER14-A-ZVG/US

Factory setting		-50...150 °C	
Resolution			
Resolution of analogue output		[K]	0.04
Accuracy / deviations			
Precision analogue output		[K]	± 0,3 + (± 0,1 % MS)
Temperature coefficient		[X22]	0,1; (in case of deviation from the reference condition 25 ± 5 °C)
Response times			
Dynamic response T05 / T09		[s]	1 / 3
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
Operating conditions			
Ambient temperature		[°C]	-25...80
Storage temperature		[°C]	-40...100
Protection		IP 67; IP 68; IP 69K	
Tests / approvals			
EMC		DIN EN 61000-6-2	
Shock resistance		DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance		DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF		[ANN]	572
UL approval		UL Approval no.	K002
Mechanical data			
Weight		[g]	94
Dimensions		[mm]	Ø 18.7
Materials		stainless steel (1.4404 / 316L); PEI; FKM	
Materials (wetted parts)		stainless steel (1.4404 / 316L); O-ring: FKM	
Tightening torque		[Nm]	35
Process connection		threaded connection G 1/4	
Probe diameter		[mm]	6
Installation length EL		[mm]	50
Displays / operating elements			
Display		operating status	1 x LED, green
Remarks			
Remarks		MS = set measuring span	
Pack quantity		1 pcs.	

TA2115

Temperature transmitter

TA-050CLER14-A-ZVG/US



Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

