


TA4019

Temperature transmitter

TA-050CLEM10-Z- ZVG/DE



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1	
Measuring range	-50...150 °C	-58...302 °F
Process connection	threaded connection M10 x 1 external thread DIN 3852 T1 FORM A (DIN 3852-1:2002-05)	
Installation length EL [mm]	50	

Application

Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)	
Media	liquids and gases	
Pressure rating [bar]	400	

Electrical data

Operating voltage [V]	10...30 DC; ("supply class 2" to cULus)	
Current consumption [mA]	< 30	
Protection class	III	
Reverse polarity protection	yes	

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1	
------------------------------	-------------------------------	--

Outputs

Total number of outputs	1	
Output signal	analogue signal	
Number of analogue outputs	1	
Analogue current output [mA]	4...20	
Max. load [Ω]	(U _b - 8,5 V) / 21,5 mA; 24 V: 720 Ω	
Short-circuit protection	yes	
Overload protection	yes	

Measuring/setting range


Measuring range	-50...150 °C	-58...302 °F
-----------------	--------------	--------------

TA4019



Temperature transmitter

TA-050CLEM10-Z- ZVG/DE

Resolution		
Resolution of analogue output	[K]	0.04
Accuracy / deviations		
Precision analogue output	[K]	$\pm 0,3 + (\pm 0,1 \% MS)$
Temperature coefficient	[X22]	0,1; (in case of deviation from the reference condition $25 \pm 5^\circ\text{C}$)
Response times		
Dynamic response T05 / T09	[s]	1 / 3; (to DIN EN 60751)
Operating conditions		
Ambient temperature	[°C]	-40...100
Storage temperature	[°C]	-40...100
Protection		IP 68; IP 69K
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[ANN]	1092
UL approval	UL Approval no.	K006
Mechanical data		
Weight	[g]	93
Materials		stainless steel (1.4404 / 316L); PPS; FKM
Materials (wetted parts)		stainless steel (1.4404 / 316L)
Process connection		threaded connection M10 x 1 external thread DIN 3852 T1 FORM A (DIN 3852-1:2002-05)
Probe diameter	[mm]	6
Installation length EL	[mm]	50
Remarks		
Remarks		The values for accuracy apply to flowing water. referring to UL: for use on a low voltage circuit with overcurrent protection in accordance with UL873 tab. 28.1 or $I_{max} = 100/U_b$ (U_b = voltage of the circuit)
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x DEUTSCH connector (DT04-3P)		
		

TA4019

Temperature transmitter

TA-050CLEM10-Z- ZVG/DE



Connection

