


SB5244



Flow meter with integrated backflow prevention and display

SBG11KL0FRKG



Product characteristics				
Measuring range	1...50 l/min	0.06...3 m³/h	16...793 gph	0.26...13.2 gpm
Process connection	threaded connection G 1 internal thread			
Application				
Special feature	Gold-plated contacts			
Media	Liquids; oils (viscosity 150 mm²/s at 40 °C)			
Medium temperature	[°C]	-10...100		
Pressure rating	[bar]	100		
Pressure rating	[MPa]	10		
Note on pressure rating	at medium temperature >70°C: 80 bar / 8 MPa			



Flow meter with integrated backflow prevention and display

SBG11KL0FRKG

Electrical data				
Operating voltage	[V]	18...30 DC; (to SELV/PELV)		
Current consumption	[mA]	< 50		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	< 3		
Outputs				
Total number of outputs		2		
Output signal		switching signal; analogue signal; frequency signal; IO-Link		
Output function		normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC	[V]	2		
Max. current load per output	[mA]	150; (200: ...60 °C; Ambient temperature; 250: ...40 °C; Ambient temperature)		
Analogue current output	[mA]	4...20		
Max. load	[Ω]	500		
Short-circuit protection		yes		
Overload protection		yes		
Frequency of the output	[Hz]	0...10000		
Measuring/setting range				
Measuring range		1...50 l/min	0.06...3 m³/h	16...793 gph
Display range		0...60 l/min	0...3.6 m³/h	0...951 gph
Resolution		0.01 l/min	0.001 m³/h	1 gph
Set point SP		0.35...50 l/min	0.02...3 m³/h	5...793 gph
Reset point rP		0...49.65 l/min	0...2.98 m³/h	0...787 gph
Frequency end point, FEP		3.35...50 l/min	0.2...3 m³/h	53...793 gph
In steps of		0.05 l/min	0.005 m³/h	1 gph
Frequency at the end point FRP	[Hz]	10...10000		
In steps of	[Hz]	10		
Measuring dynamics		1:50		
Temperature monitoring				
Measuring range		-10...100 °C	14...212 °F	
Display range		-32...122 °C	-25.6...251.6 °F	
Resolution		0.1 °C	0.1 °F	
Set point SP		-9.3...100 °C	15.2...212 °F	
Reset point rP		-10...99.3 °C	14...210.8 °F	
In steps of		0.1 °C	0.2 °F	
Frequency start point, FSP		-10...78 °C	14...172.4 °F	
Frequency end point, FEP		12...100 °C	53.6...212 °F	
Frequency at the end point FRP	[Hz]	10...10000		
In steps of	[Hz]	10		
Accuracy / deviations				
Flow monitoring				
Accuracy (in the measuring range)		± 5 % MEW; (Q > 1 l/min; 20...70 °C Medium temperature)		



Flow meter with integrated backflow prevention and display

SBG11KL0FRKG

Repeatability	± 1 % MEW	
Temperature monitoring		
Temperature drift	0,029 °C / K	
Accuracy	[K]	3 K (25°C; Q > 1 l/min)
Response times		
Flow monitoring		
Response time	[s]	0.01
Damping process value dAP	[s]	0...5
In steps of	[s]	0.1
Damping for the analogue output dAA	[s]	0...5
In steps of	[s]	0.1
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 120 (Q > 1 l/min)
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; current/frequency output; damping for the switching output / analogue output; display can be rotated and switched off; standard unit of measurement; process value colour; calibration factor	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	yes	
Required master port type	A	
Process data analogue	2	
Process data binary	2	
Min. process cycle time	[ms]	3.2
Supported DeviceIDs	Type of operation	DeviceID
	default	1045
Operating conditions		
Ambient temperature	[°C]	0...60
Note on ambient temperature	medium temperature < 80 °C	
	medium temperature < 100 °C: 0...40 °C	
Storage temperature	[°C]	-15...80
Protection	IP 65; IP 67	
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[ANN]	170
UL approval	UL Approval no.	I006
Pressure Equipment Directive	Sound engineering practice	



Flow meter with integrated backflow prevention and display

SBG11KL0FRKG

Mechanical data		
Weight	[g]	1571.5
Materials	stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated	
Materials (wetted parts)	stainless steel (316 / 1.4401); stainless steel (1.4404 / 316L); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM	
Process connection	threaded connection G 1 internal thread	
Switching cycles mechanical	10 million	

Displays / operating elements		
Display	Display unit	6 x LED, green
	switching status	2 x LED, yellow
	measured values	alphanumeric display, red/green alternating indication 4-digit
	programming	alphanumeric display, 4-digit

Remarks		
Remarks	Recommendation: use a 200-micron filter.	
	All data refer to oil with the following nominal viscosity: 150 cSt, 40 °C ± 3 K	
	MW = measured value	
	MEW = Final value of the measuring range	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated





Flow meter with integrated backflow prevention and display

SBG11KL0FRKG

Connection



OUT1:

- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- frequency output volumetric flow quantity monitoring
- frequency output Temperature monitoring
- IO-Link

OUT2:

- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- analogue output volumetric flow quantity monitoring
- analogue output Temperature monitoring
- colours to DIN EN 60947-5-2

Core colours :

BK = black
BN = brown
BU = blue
WH = white

Diagrams and graphs

