


TAP961



Temperature transmitter

TAP040KLES30-PRAVG/US/

Article no longer available - archive entry



- 1 sealing area
- 2 Aseptoflex thread



EHEDG Certified

Product characteristics

Measuring range	-25...150 °C	-13...302 °F
Process connection	G 1 Aseptoflex Vario	

Application

Special feature	Gold-plated contacts
Measuring element	1 x Pt 1000 + 1 x NTC; (thermically coupled, with backup function (temperature measuring even if one element fails))
Application	suitable for all standard CIP and SIP processes
Media	liquids and gases
Pressure rating [bar]	50
Minimum installation depth [mm]	15
No dead space	yes

Electrical data

Operating voltage [V]	9...32 DC; (to SELV/PELV)
Current consumption [mA]	< 15.6; (max. fault current : 21,8)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	35
Integrated watchdog	yes

Outputs

Overload protection	yes
---------------------	-----

Measuring/setting range

Probe length L [mm]	40
---------------------	----

TAP961



Temperature transmitter

TAP040KLES30-PRAVG/US/

Measuring range	-25...150 °C	-13...302 °F
Drift warning	0.2...5 °C	0.4...9 °F
Drift alarm	0.2...5 °C	0.4...9 °F
In steps of	0.05 °C	0.1 °F
Accuracy / deviations		
Drift monitoring [K]	± 0,2 (-10...100°C); ± 0,3 (-25...-10/100...150°C) *); (probe completely inserted into the measured medium up to the sealing chamfer)	
Temperature coefficient [X22]	< ± 0,01; (in case of deviation from the reference condition 25 ± 5 °C)	
Response times		
Dynamic response T05 / T09 [s]	6 / 13	
Max. measuring/display cycle [ms]	600	
Software / programming		
Parameter setting options	parameter setting to PROFIBUS PA profile temperature transmitter, version 3.01; I&M-Parameter; drift and diagnostic function	
Operating conditions		
Ambient temperature [°C]	-25...70	
Note on ambient temperature	electronics: -25...70 °C	
	Process connection: -32...170 °C	
Storage temperature [°C]	-40...85	
Protection	IP 68; IP 69K	
Tests / approvals		
EMC	DIN EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
Note on approval	Including free 5-point calibration certificate.	
Mechanical data		
Materials	stainless steel (1.4404 / 316L); PEI; FKM	
Materials (wetted parts)	stainless steel (1.4404 / 316L)	
Process connection	G 1 Aseptoflex Vario	
Surface characteristics Ra/Rz of the wetted parts	Ra: < 0.6	
Remarks		
Remarks	n.c. = not used	
	operating voltage "supply class 2" according to cULus	
	9...24 V DC when used inside the hazardous area	
Pack quantity	1 pcs.	

TAP961




Temperature transmitter

TAP040KLES30-PRAVG/US/

Electrical connection

Connection



Connector: 1 x M12; Contacts: gold-plated