

# SR0125




## Control monitor for flow sensors

VS0200 TYP VR31D -25 bis +60G

Article no longer available - archive entry

Alternative articles: SR0126  
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Application	Flow monitoring; Wire monitoring	
Electrical data		
Operating voltage tolerance	[%]	-20...20
Operating voltage	[V]	24 DC
Current consumption	[mA]	70
Power-on delay time	[s]	30
Number of channels		1
Outputs		
Electrical design	relay	
Contact rating	4 A, 250 V AC	
Switching function flow monitoring	relay energised when flow is present	
Switching function wire break monitoring	relay de-energised in case of wire break	
Response times		
Response time	[s]	< 10
Software / programming		
Adjustment of the switch point	potentiometer	
Selection liquids / gases	slide switch	

# SR0125



## Control monitor for flow sensors

VS0200 TYP VR31D -25 bis +60G

### Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 40
Protection rating terminals		IP 20

### Mechanical data

Housing		housing for DIN rail mounting
Dimensions	[mm]	75 x 55 x 110
Materials		plastics

### Displays / operating elements

Display	function	11 x LED
	switching status	LED, red


### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

terminals: 16 x ...2.5 mm<sup>2</sup>

### Connection



- 1: Relais Wire monitoring  
2: Relais Flow monitoring  
Core colours :

BN = brown  
BU = blue  
BK = black  
WH = white  
GY = grey