


ST2610

Flow monitor

SCN14ABAFPKG/PH



Article no longer available - archive entry



Product characteristics		
Number of inputs and outputs		Number of digital outputs: 1
Process connection		1/4" NPT
Application		
Media		Liquids
Medium temperature	[°C]	-25...80
Pressure rating	[bar]	30
Electrical data		
Operating voltage	[V]	20...36 DC
Current consumption	[mA]	< 45
Reverse polarity protection		yes
Power-on delay time	[s]	< 20
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 1
Outputs		
Total number of outputs		1
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		1
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5

ST2610



Flow monitor

SCN14ABAFPKG/PH

Permanent current rating of switching output DC	[mA]	400
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60
Accuracy / deviations		
Temperature gradient	[K/min]	15
Response times		
Response time	[s]	1...10
Software / programming		
Adjustment of the switch point		potentiometer
Operating conditions		
Ambient temperature	[°C]	-20...80
Protection		IP 67
Mechanical data		
Materials		PBT-GF20
Materials (wetted parts)		stainless steel (1.4305 / 303)
Process connection		1/4" NPT
Displays / operating elements		
Display	function	11 x LED
Аксессуары		
Items supplied		screwdrivers
Remarks		
Pack quantity		1 pcs.

ST2610





Flow monitor

SCN14ABAFPKG/PH

Electrical connection

Cable: 2 m, PUR; 3 x 0.5 mm², PVC

Connection



BN =
BU =
BK =

Core colours :
brown
blue
black