


Flow sensor for connection to an evaluation unit

STR12ABBE1/6M

Article no longer available - archive entry



Product characteristics

Process connection	G 1/2 external thread
--------------------	-----------------------

Application

Application	Ex zone 1
Medium temperature [°C]	-25...80
Pressure rating [bar]	30

Liquids

Application	Ex zone 1
Medium temperature [°C]	-25...80

Gases

Medium temperature [°C]	-25...80
-------------------------	----------

Electrical data

Connection to control monitor	VS 0100 Ex
-------------------------------	------------

Measuring/setting range

Liquids

Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60

Gases

Setting range [cm/s]	200...2000
Greatest sensitivity [cm/s]	100...800

Accuracy / deviations

Temperature gradient [K/min]	15
------------------------------	----

Response times

Response time [s]	1...10
-------------------	--------


ST3211



Flow sensor for connection to an evaluation unit

STR12ABBE1/6M

Liquids	
Response time	[s] 1...10
Gases	
Response time	[s] 1...10
Operating conditions	
Protection	IP 67
Mechanical data	
Housing	threaded type
Materials	stainless steel (1.4571/316Ti)
Process connection	G 1/2 external thread
Remarks	
Pack quantity	1 pcs.
Electrical connection	
Cable: 6 m, PUR; 4 x 0.34 mm ²	
Connection	



	Core colours :
BN =	brown
GN =	green
WH =	white
YE =	yellow