


## Flow sensor for connection to an evaluation unit

STR34ABA/US-100-H

Article no longer available - archive entry



## Product characteristics

Process connection	G 3/4 external thread
--------------------	-----------------------

## Application

Application	high-temperature range
Media	Liquids; Gases
Medium temperature [°C]	-25...80
Pressure rating [bar]	30

## Liquids

Application	high-temperature range
Medium temperature [°C]	-25...80

## Gases

Medium temperature [°C]	-25...80
-------------------------	----------

## Electrical data

Connection to control monitor	VS 0100
-------------------------------	---------

## Measuring/setting range

## Liquids

Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60

## Gases

Setting range [cm/s]	5...1500
----------------------	----------

## Accuracy / deviations

Temperature gradient [K/min]	15
------------------------------	----

# ST4004



## Flow sensor for connection to an evaluation unit

STR34ABA/US-100-H

### Response times

Response time	[s]	1...10
---------------	-----	--------

### Liquids

Response time	[s]	1...10
---------------	-----	--------

### Gases

Response time	[s]	1...10
---------------	-----	--------

### Operating conditions

Protection	IP 67
------------	-------

### Mechanical data

Housing	threaded type
---------	---------------

Materials	stainless steel (1.4305 / 303)
-----------	--------------------------------

Process connection	G 3/4 external thread
--------------------	-----------------------

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Connector: 1 x M12; coding: A; Maximum cable length: 100 m



### Connection

