




Product characteristics

Frequency range	[Hz]	0.1...12000
Communication interface		Ethernet

Application

Design	parameter setting via PC software VES004
Application	continuous vibration monitoring

Electrical data

Operating voltage tolerance	[%]	20
Operating voltage	[V]	24 DC; (when using the IEPE input: 24 V + 20%; IEPE = Integrated Electronics Piezo Electric)
Current consumption	[mA]	200; (24 V)
Protection class		III

Inputs / outputs

Total number of inputs and outputs	16; (configurable)
Number of inputs and outputs	Number of digital inputs: 8; Number of analogue inputs: 2; number of dynamic inputs: 4; Number of digital outputs: 10; Number of analogue outputs: 1

Inputs

Total number of inputs	10
Number of digital inputs	8; (configurable)
Input circuit of digital inputs	HTL
Number of analogue inputs	2



Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS

Analogue input (current)	[mA]	4...20
Resolution of analogue input		12
Number of dynamic inputs		4
Dynamic input - signal		0...10 mA / IEPE / 4...20 mA
Dynamic input - resolution	[bit]	16
Dynamic input - frequency range	[Hz]	0,1...12000
Dynamic input - sampling rate	[kSamples]	100

Outputs		
Total number of outputs		10
Output signal		switching signal; analogue signal
Electrical design		PNP
Number of digital outputs		10; (configurable)
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	100
Number of analogue outputs		1; (configurable)
Analogue current output	[mA]	0...22; (0...10 V)
Max. load	[Ω]	500
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Measuring/setting range		
Frequency range	[Hz]	0.1...12000

Interfaces		
Communication interface		Ethernet
Protocol		TCP/IP

Operating conditions		
Ambient temperature	[°C]	0...70
Storage temperature	[°C]	0...70
Protection		IP 20

Tests / approvals		
EMC	EN IEC 61000-6-2	
	EN IEC 61000-6-4	
MTTF	[ANN]	89
UL approval	Ta	70 °C
	Enclosure type	Type 1
	подача напруги	Limited Voltage/Current
	File number UL	E251902

Mechanical data		
Weight	[g]	442.6



Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS

Housing	plastic housing
Type of mounting	rail; (TH35/EN60715)
Dimensions [mm]	114 x 50 x 105
Materials	PA
Data memories	
History memory	yes
Data memory buffered	yes
Data memory type	ring memory; FIFO
Real-time clock	yes
Memory location	internal
Memory interval	min. 1 min
Memory size	881664 data records
Аксесуари	
Accessories (optional)	cross-over Ethernet patch cable for the direct connection to the PC
Remarks	
Pack quantity	1 pcs.

Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS

Electrical connection

COMBICON: ; Maximum cable length: 250 m

Connection

