


Inductive sensor

IEA2001-AROG/5M/US

Article no longer available - archive entry



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	1
Housing	threaded type
Dimensions [mm]	M8 x 1

Electrical data

Operating voltage [V]	5...36 DC
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	4
Max. leakage current [mA]	0.8
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	2000
Short-circuit protection	no
Overload protection	no

XC0014



Inductive sensor

IEA2001-AROG/5M/US

Detection zone		
Sensing range	[mm]	1
Real sensing range Sr	[mm]	1 ± 10 %
Operating distance	[mm]	0...0.8
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1
Thread designation		M8 x 1
Materials		brass nickel-plated; PBT
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		
Cable: 5 m, PUR		
Connector: 1 x M12; coding: A		

XC0014

Inductive sensor

IEA2001-AROG/5M/US



Connection

