

Contr 2MSTR 1RS232C 1RS485

Technical drawing of the RS485 interface module, showing front and side views with dimensions.

Front View Dimensions:

- Width: 50
- Height: 130
- Terminal block labels: ASI 2+, ASI 2-, +24 V, 0 V, ASI 1+, ASI 1-, PE
- Buttons: ALARM, CONFIRM, NOT AUTO, ADDR, MODIF, SET
- Display: 2228
- Buttons: ASI PWR, COM, MODE, PROG, MODE, CTRL

Side View Dimensions:

- Width: 113
- Height: 47,5
- Bottom flange height: 3
- Bottom flange width: 120

Labels:

- 1 Programming interface RS232C
- 2 Datenschnittstelle RS485



Application	Mini-controller for signal preprocessing
-------------	--

Application	Mini-controller for signal preprocessing
-------------	--

Operating voltage	[V]	22...30 DC; (24 DC ; to PELV)
Insulation rating	[V]	500
Max. current consumption from AS-i	[mA]	80
Electrical separation		yes

Electrical design	AS-i
-------------------	------

Electrical design	AS-i
-------------------	------

Communication interface	RS232
-------------------------	-------

Communication interface	RS232
-------------------------	-------

Number of R232 interfaces	1
Transmission rate	4800...62400 Baud
Type of connector	SUB-D
Usage type	Programming

Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Protection		IP 20

AC1012



AS-Interface PLC

Contr 2MSTR 1RS232C 1RS485

Tests / approvals		
Shock/vibration resistance	< 15 g (11ms) / < 55 Hz (0.5mm)	
AS-i classification		
AS-i master profile	M1	
AS-i certificate	22505	
Mechanical data		
Housing	housing for DIN rail mounting	
Material	aluminum	
Displays / operating elements		
Display	function check	2 x LED, red
		2 x LED, green
		2 x LED, yellow
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
screw terminals: 7 x		
Connection		

7	AS-i 2+
6	AS-i 2-
5	+ 24 V
4	0 V
3	AS-i 1+
2	AS-i 1-
1	PE