


AC1304



AS-Interface PLC

ControllerE 2Mstr 1RS232C

Article no longer available - archive entry



Application	
Application	decentralized controller
Electrical data	
Operating voltage [V]	24 DC; (cULus - Class 2 source required)
Insulation rating [V]	500
Current consumption [mA]	< 500
Max. current consumption from AS-i [mA]	10
Max. power consumption [VA]	10
Number of AS-i masters	2
Electrical separation	yes
Interfaces	
Communication interface	RS232
RS232	
Number of R232 interfaces	1
Transmission rate	9600...115200 Baud
Type of connector	RJ11

AC1304



AS-Interface PLC

ControllerE 2Mstr 1RS232C

Usage type	Programming
Note on interfaces	electrically isolated

Operating conditions

Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Max. relative air humidity	[%]	95
Protection		IP 20

AS-i classification

AS-i version	2.1
AS-i master profile	M3
AS-i certificate	61102

Mechanical data

Weight	[g]	517.4
Housing		housing for DIN rail mounting
Dimensions	[mm]	86 x 131 x 107
Material		aluminum; steel sheet galvanized

Displays / operating elements

Display	Function	2 x LED, red
		3 x LED, green
		3 x LED, yellow
		full graphic LCD display

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connection

