


AC1308



AS-Interface DeviceNet gateway with PLC

ControllerE 1Master DN RS232

Article no longer available - archive entry



Application

Application	decentralized controller; DeviceNet gateway
-------------	---

Electrical data

Operating voltage	[V]	24 DC
Current consumption	[mA]	500
Max. current consumption from AS-i	[mA]	10
Max. power consumption	[VA]	10
Number of AS-i masters		1

Interfaces

Communication interface	RS232; CAN
CAN	
Protocol	DeviceNet
Usage type	Data transmission
Note on interfaces	Group 2 only Slave

AC1308



AS-Interface DeviceNet gateway with PLC

ControllerE 1Master DN RS232

RS232		
Number of R232 interfaces		1
Transmission rate		9600...115200 Baud
Type of connector		RJ11
Usage type		Programming
Note on interfaces		electrically isolated

Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Max. relative air humidity	[%]	95
Protection		IP 20

AS-i classification		
AS-i version		2.1
AS-i master profile		M3
AS-i certificate		61111

Mechanical data		
Housing		housing for DIN rail mounting
Material		aluminum; steel sheet galvanized

Displays / operating elements		
Display	Function	3 x LED, red
		4 x LED, green
		2 x LED, yellow
		full graphic LCD display

Remarks		
Pack quantity		1 pcs.

Electrical connection		
Connection		

