


AC1314



AS-Interface DeviceNet gateway with PLC

ControllerE 2Master DN RS232

Article no longer available - archive entry



Application	
Application	decentralized controller; DeviceNet gateway
Electrical data	
Operating voltage	[V] 24 DC
Current consumption	[mA] < 500
Max. current consumption from AS-i	[mA] 10
Max. power consumption	[VA] 10
Number of AS-i masters	2
Interfaces	
Communication interface	RS232; CAN
CAN	
Protocol	DeviceNet
Usage type	Data transmission
Note on interfaces	Group 2 only Slave



AS-Interface DeviceNet gateway with PLC

ControllerE 2Master DN RS232

RS232	
Number of R232 interfaces	1
Transmission rate	9600...115200 Baud
Type of connector	RJ11
Usage type	Programming
Note on interfaces	electrically isolated

Operating conditions

Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Max. relative air humidity	[%]	95
Protection		IP 20

AS-i classification

AS-i version	2.1
AS-i master profile	M3
AS-i certificate	61112

Mechanical data

Weight	[g]	549.4
Housing		housing for DIN rail mounting
Material		aluminum; steel sheet galvanized

Displays / operating elements

Display	Function	4 x LED, red
		3 x LED, green
		3 x LED, yellow
		full graphic LCD display

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connection

