


AC1317



AS-Interface EtherNet/IP gateway with PLC

Control.E 2Mstr ET IP RS232

Article no longer available - archive entry



Application	
Application	Use as decentralized controller and Ethernet IP Gateway / Web-Server
Electrical data	
Operating voltage [V]	24 DC; (cULus - Class 2 source required)
Current consumption [mA]	< 400
Max. current consumption from AS-i [mA]	10
Max. power consumption [VA]	10
Number of AS-i masters	2
Interfaces	
Communication interface	RS232; Ethernet
Ethernet	
Transmission rate	10; 100
Protocol	EtherNet/IP; IP
Usage type	Data transmission
Note on interfaces	CIP protocol EtherNet/IP server group 2 and group 3

AC1317



AS-Interface EtherNet/IP gateway with PLC

Control.E 2Mstr ET IP RS232

RS232		
Number of R232 interfaces	1	
Transmission rate	9600...115200 Baud	
Type of connector	RJ11	
Usage type	Programming	
Note on interfaces	electrically isolated	
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Max. relative air humidity	[%]	95
Protection	IP 20	
AS-i classification		
AS-i version	2.1	
AS-i master profile	M1e	
Mechanical data		
Housing	housing for DIN rail mounting	
Material	aluminum; steel sheet galvanized	
Displays / operating elements		
Display	Function	3 x LED, red
		4 x LED, green
		2 x LED, yellow
		full graphic LCD display
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Connection		

