




AS-Interface module

Moduloberteil aktiv, 2E/2A PNP

Article no longer available - archive entry

Alternative articles: AC5211
When selecting an alternative article and accessories please note that technical data may differ!



1 panel for labelling



Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 135
Max. current load total	[A]	2
Integrated watchdog		no
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 2; Number of digital outputs: 2
Inputs		
Number of digital inputs		2
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Voltage supply	[V]	20...30
Max. total current rating of inputs	[mA]	100
Input current High	[mA]	> 5
Input current low	[mA]	< 1.5
Switching level high	[V]	> 10
Digital inputs protected against short circuits		yes



AS-Interface module

Moduloberteil aktiv, 2E/2A PNP

Outputs					
Electrical design	AS-i				
Number of digital outputs	2				
Circuit	PNP				
Voltage range DC [V]	24; (to PELV; via M12 connector)				
Max. current load per output [mA]	1000				
Short-circuit proof	yes				
Electrically separated	yes				
Operating conditions					
Ambient temperature [°C]	-25...85				
Protection	IP 67				
Tests / approvals					
EMC	EN 50295				
AS-i classification					
AS-i profile	S-3.0				
AS-i I/O configuration [hex]	3				
AS-i ID code [hex]	0				
AS-i certificate	04201				
Data bits	Data bit	D0	D1	D2	D3
	Socket	I-1	I-2	O-3	O-4
	Pin	2+4	2+4	4	4
Mechanical data					
Type of mounting	AS-i interface to FC lower parts				
Material	PBT				
Displays / operating elements					
Display	Power	LED, green			
	Function	LED, yellow			
Remarks					
Remarks	Inputs and outputs must be electrically isolated.				
Pack quantity	1 pcs.				



AS-Interface module

Moduloberteil aktiv, 2E/2A PNP

Electrical connection

contact pins to module lower part, FK / PG:

Connector: M12; coding: A
Connector: M12; coding: A



1	External voltage +
3	External voltage -
	Inputs
1	Sensor supply L+
2+4	Data input internally bridged
3	Sensor supply L-