

AC2088




AS-Interface illuminated pushbutton module

EMS-Module 2BI 2LO

Article no longer available - archive entry

Alternative articles: AC2398

When selecting an alternative article and accessories please note that technical data may differ!



- 1 panel for labelling
- 2 LED
- 3 pushbutton 2 normally open / green
- 4 pushbutton 1 normally closed / red



Application		
Application		field installation
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	55
Inputs		
Sensor supply of the inputs		AS-i
Operating conditions		
Ambient temperature	[°C]	-25...60
Storage temperature	[°C]	-40...85
Protection		IP 67
Tests / approvals		
EMC	EN 50295	
AS-i classification		
AS-i version		2.1



AS-Interface illuminated pushbutton module

EMS-Module 2BI 2LO

Extended addressing mode	yes				
AS-i master profile	M2; M3; M4				
AS-i profile	S-B.A.E				
AS-i I/O configuration [hex]	B				
AS-i ID code [hex]	A.E				
AS-i certificate	49203				
Data bits	Data bit	D0	D1	D2	D3
	LED	1	2	-	-
	pushbutton	-	-	1	2

Mechanical data

Weight [g]	97				
Type of mounting	AS-i interface to FC and SC lower parts				
Material	PBT				

Displays / operating elements

Display	Power	LED, green			
	errors	LED, red			

Accessories

Accessories (optional)	Cover removal tool:, E70206				
------------------------	-----------------------------	--	--	--	--

Remarks

Remarks	The pushbuttons (EAO type 84) provide protection against accidental contact.				
	Housing and pushbuttons can be labeled.				
Pack quantity	1 pcs.				

Electrical connection

contact pins to module lower part, FK / PG:					
---	--	--	--	--	--