


Temperature sensor with display

TN-013KBBBD10-MFPKG/US/ IV

Article no longer available - archive entry



- 1 7-segment LED display
- 2 programming button
- 3 internal thread M18 x 1.5



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1	
Measuring range	-40...125 °C	-40...257 °F
Process connection	threaded connection M18 x 1,5 internal thread	

Application

Special feature	Gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class B)	
Application	detection of surface temperatures	
Media	liquids and gases	
Pressure rating [bar]	30	
Minimum installation depth [mm]	15	

Electrical data

Operating voltage [V]	20...30 DC	
Current consumption [mA]	< 66	
Min. insulation resistance [MΩ]	100; (500 V DC)	
Protection class	III	



Temperature sensor with display

TN-013KBBD10-MFPKG/US/ IV

Reverse polarity protection	yes
Power-on delay time [s]	1.5
Integrated watchdog	yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1
------------------------------	---

Outputs

Total number of outputs	2
Output signal	switching signal; analogue signal; (configurable)
Electrical design	PNP
Number of digital outputs	1
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	250
Number of analogue outputs	1
Analogue current output [mA]	4...20
Max. load [Ω]	500
Analogue voltage output [V]	0...10
Min. load resistance [Ω]	2000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Measuring/setting range

Probe length L [mm]	45
Measuring range	-40...125 °C -40...257 °F
Set point SP	-39.5...125 °C -39...257 °F
Reset point rP	-40...124.5 °C -40...256 °F
Analogue start point	-40...115 °C -40...239 °F
Analogue end point	-30...125 °C -22...257 °F
In steps of	0.5 °C 1 °F

Resolution

Resolution of switching output [K]	0.5
Resolution of analogue output [K]	0.125
Resolution of display [K]	0.5

Accuracy / deviations

Switch point accuracy [K]	$\pm$ (Pt 1000 + 0,2 K)
Precision analogue output [K]	$\pm$ (Pt 1000 + 0,2 K + 0,4%)
Display accuracy [K]	$\pm$ (Pt 1000 + 0,2 K + ½ Digit)
Temperature drift per 10 K [K]	0.1

Response times

Dynamic response T05 / T09 [s]	1 / 3; (to DIN EN 60751)
Max. measuring/display cycle [ms]	200



Temperature sensor with display

TN-013KBBD10-MFPKG/US/ IV

Software / programming		
Adjustment of the switch point	programming button	
Parameter setting options	hysteresis / window; normally open / normally closed; min/max memory reset; Display unit; zero-point calibration; analogue output selectable and scalable	
Operating conditions		
Ambient temperature	[°C]	-25...70
Storage temperature	[°C]	-40...100
Protection	IP 67	
Tests / approvals		
EMC	DIN EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
Mechanical data		
Housing	compact type for adapter	
Materials	stainless steel (1.4301 / 304); PBT; PC; EPDM/X; FKM	
Materials (wetted parts)	stainless steel (1.4404 / 316L)	
Process connection	threaded connection M18 x 1,5 internal thread	
Displays / operating elements		
Display	switching status	LED, red
	function display	7-segment LED display
	measured values	7-segment LED display
Remarks		
Remarks	The values for accuracy apply to flowing water.	
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x M12; coding: A; Contacts: gold-plated		
		

TN2930



Temperature sensor with display

TN-013KBBD10-MFPKG/US/ IV

Connection

