


AC5271



AS-Interface Airbox with quick mounting technology

AirBox 5/3 closed 4DI-Y AUX



Application	
Application	field installation
Medium temperature [°C]	-10...50
Electrical data	
Operating voltage [V]	26.5...31.6 DC
Max. current consumption from AS-i [mA]	280
Additional voltage supply [V]	18...30 DC; (to PELV)
Additional voltage supply	required
Max. current consumption from additional supply [mA]	10
Integrated watchdog	yes
Inputs / outputs	
Number of inputs and outputs	Number of digital inputs: 4; Number of pneumatic outputs: 2



AS-Interface Airbox with quick mounting technology

AirBox 5/3 closed 4DI-Y AUX

Inputs						
Number of digital inputs	4					
Input circuit of digital inputs	PNP					
Sensor supply of the inputs	AS-i					
Voltage supply [V]	20...30; (via flat cable)					
Max. total current rating of inputs [mA]	200					
Input current High [mA]	6...10					
Input current low [mA]	0...2					
Switching level high [V]	> 11					
Digital inputs protected against short circuits	yes					
Outputs						
Number of pneumatic outputs	2; (supply: external 24 V power supply)					
Actuator supply outputs	AUX					
Operating conditions						
Ambient temperature [°C]	-10...55					
Protection	IP 65; IP 67					
Tests / approvals						
EMC	EN 50295					
	IEC 61000-6-2					
MTTF [years]	216					
AS-i classification						
AS-i version	2.11; 3.0					
AS-i addressing	Addressing socket					
Extended addressing mode	yes					
AS-i master profile	M2; M3; M4					
AS-i profile	S-7.A.E					
AS-i I/O configuration [hex]	7					
AS-i ID code [hex]	A.E					
Data bits	Data bit	D0	D1	D2	D3	
	Input	1	2	3	4	
	Socket	I-1/2	I-1/2 I-2	I-3/4	I-3/4 I-4	
	Pin	4	2 4	4	2 4	
	pneumatic output	2	4	-	-	
Mechanical data						
Weight [g]	384					
Type of mounting	quick mounting					
Material	PA; POM; Piercing contacts: CuSn6 nickel-plated and tin-plated					
Pneumatic system	1 x 5/3-way slide valve (free from overlapping); middle position blocked					
Operating pressure range [bar]	3...8					
Operating pressure range [MPa]	0.3...0.8					
Operating pressure range [psi]	43.5...116					
Air flow at 6/5 bar [l/min]	400					
Permissible compressed air	non-lubricated compressed air class 6-3-1; lubricated compressed air class 6-3-4					

AC5271



AS-Interface Airbox with quick mounting technology

AirBox 5/3 closed 4DI-Y AUX

Manual override	pressing/releasing or pressing/turning/locking	
Tube fittings	8 mm	
Exhaust	exhaust can be discharged through tube connection	
Displays / operating elements		
Display	Power	LED, green
	errors	LED, red
	Function	LED, yellow
Electrical connection		
Module connection	Flat cable	
Accessories		
Items supplied	lower part	
Accessories (optional)	Mounting plate:, E74999	
	Module lower part:, E75000	
	Protective cap: M12, E73004	
	sealing plug:, E75231	
	Silencer:, E75232	
	Push-in L-fitting:, E75228	
	Push-in T-fitting:, E75227	
Remarks		
Remarks	If not pneumatically operated, E75231 sealing plug must be inserted.	
	Avoid ingress of dirt and dust.	
	Do not connect any of the following points to an external potential:	
	L-, L+, I-1, I-2, I-3, I-4	
	The connections are electrically connected with the AS-i cable.	
	Please see the notes on compressed air and EMC/ESD under "Downloads"	
Pack quantity	1 pcs.	




AS-Interface Airbox with quick mounting technology

AirBox 5/3 closed 4DI-Y AUX

Electrical connection

quick mounting technology for AS-i flat cable: ; three selectable directions

Connection



Connector: M12

Inputs	
Socket I-1/2	
1	Sensor supply L+
2	Data input 2
3	Sensor supply L-
4	Data input 1
5	not used
Socket I-2	
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	Data input 2
5	not used
Socket I-3/4	
1	Sensor supply L+
2	Data input 4
3	Sensor supply L-
4	Data input 3
5	not used
Socket I-4	
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	Data input 4
5	not used




AS-Interface Airbox with quick mounting technology

AirBox 5/3 closed 4DI-Y AUX

Diagrams and graphs

Pneumatic symbol



1 x 5/3-way slide valve (free from overlapping); middle position blocked