
AC5290

AS-Interface ClassicLine module with quick mounting technology

ClassicLine 4DI-Y AUX IP67



Application		
Application		field installation
Electrical data		
Operating voltage	[V]	26.5...31.6 DC; (cULus - Class 2 source required)
Max. current consumption from AS-i	[mA]	30
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 4
Inputs		
Number of digital inputs		4
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AUX
Voltage supply	[V]	20...30; (via flat cable)
Max. total current rating of inputs	[mA]	1000
Input current High	[mA]	6...10
Input current low	[mA]	0...2
Switching level high	[V]	> 11
Digital inputs protected against short circuits		yes
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67

AC5290

AS-Interface ClassicLine module with quick mounting technology

ClassicLine 4DI-Y AUX IP67

Tests / approvals

EMC		EN 50295					
		IEC 61000-6-2					
MTTF	[years]	225					

AS-i classification

AS-i version		2.11; 3.0					
AS-i addressing		Addressing socket					
Extended addressing mode		yes					
AS-i master profile		M2; M3; M4					
AS-i profile		S-0.A.E					
AS-i I/O configuration	[hex]	0					
AS-i ID code	[hex]	A.E					
Data bits		Data bit	D0	D1	D2	D3	
		Input	1	2	3	4	
		Socket	I-1/2	I-1/2 I-2	I-3/4	I-3/4 I-4	
		Pin	4	2 4	4	2 4	
Parameter bits		Parameter bit	Description				
		P0	not used				
		P1	peripheral fault indication	: 1	activated	* / 0	disabled
		P2	not used				
		P3	not used				

Mechanical data

Weight	[g]	173	
Type of mounting		AS-i flat cable connection	
Material		PA; Piercing contacts: CuSn6 nickel-plated and tin-plated	

Displays / operating elements

Display		Power	LED, green Voltage AUX > 7 V
		errors	LED, red AUX 15 V ± 2 V
		Function	LED, yellow

Electrical connection

Module connection		Flat cable

Accessories

Items supplied		lower part
Accessories (optional)		Protective cap: M12, E73004

Remarks

Pack quantity		1 pcs.

AC5290


AS-Interface ClassicLine module with quick mounting technology

ClassicLine 4DI-Y AUX IP67

Electrical connection

quick mounting technology for AS-i flat cable: ; three selectable directions

Connection



Connector: M12

	Inputs
	Socket I-1/2
1	Sensor supply L+
2	Data input 2
3	Sensor supply L-
4	Data input 1
5	not used
	Socket I-2
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	Data input 2
5	not used
	Socket I-3/4
1	voltage supply L+
2	Data input 4
3	Sensor supply L-
4	Data input 3
5	not used
	Socket I-4
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	Data input 4
5	not used