


TS2229



Temperature cable sensor with bolt-on sensor

TS-PT100 CONTACT SENSOR



Product characteristics

Measuring range	-40...90 °C	-40...194 °F
Process connection	bolt-on sensor 12 x 8,7 x 51 mm	

Application

Special feature	Gold-plated contacts
Measuring element	1 x Pt 100; (to DIN EN 60751, class A)
Installation	surface mount RTD for solid bodies

Electrical data

Insulation rating	[M]	2500; (insulation between sensor housing and internal structure of the sensor)
Protection class		III

Measuring/setting range

Measuring range	-40...90 °C	-40...194 °F
-----------------	-------------	--------------

Accuracy / deviations

Accuracy	[K]	$\pm (0,15 K + 0,002 \times t)$
----------	-----	-----------------------------------

Response times

Dynamic response T05 / T09	[s]	9 / 15; (values for a flat aluminium surface (anodised) using a conductive heat paste; reference values for moving water : 10 / 24 (< 0,1 m/s))
----------------------------	-----	---

Operating conditions

Protection	IP 67
------------	-------

Tests / approvals

MTTF	[ANN]	11415.5
------	-------	---------

Mechanical data

Weight	[g]	88.5
Housing		bolt-on sensor
Dimensions	[mm]	12 x 8.7 x 51
Materials		stainless steel (1.4303 / 305 / 308); copper nickel-plated
Process connection		bolt-on sensor 12 x 8,7 x 51 mm

TS2229



Temperature cable sensor with bolt-on sensor

TS-PT100 CONTACT SENSOR

Remarks

Pack quantity

1 pcs.

Electrical connection

Cable: 2 m, PUR, Ø 4.9 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

