




## Evaluation unit for speed monitoring

D100/230VAC/WINDOW

Article no longer available - archive entry



1 Mounting on DIN rail



## Product characteristics

Housing	housing for DIN rail mounting
Dimensions [mm]	75 x 55 x 110

## Application

Application	universal evaluation of pulse sequences with regard to overspeed and underspeed; Rotational speed monitoring
-------------	--

## Electrical data

Nominal voltage AC [V]	< 230
Nominal voltage DC [V]	24
Nominal voltage tolerance [%]	10
Nominal voltage tolerance 2 [%]	10
Nominal frequency AC [Hz]	50...60
Auxiliary energy for sensors DC [V]	24; ( $\leq 30$ mA)

## Inputs / outputs

Number of inputs and outputs	Number of relay outputs: 2
------------------------------	----------------------------

## Outputs

Number of relay outputs	2
Contact rating	8 A / 1250 VA / 250 V AC

## Measuring/setting range

Setting range [Imp/min]	100...1000
-------------------------	------------

## Accuracy / deviations

Hysteresis [% of Sr]	5
Repeatability [% of Sr]	1



## Evaluation unit for speed monitoring

D100/230VAC/WINDOW

Reaction times		
Start-up delay	[s]	0.5...15
Software / programming		
Adjustment of the switch point	fine adjustment within the range with potentiometer	
Operating conditions		
Ambient temperature	[°C]	-20...70
Protection	IP 40	
Protection rating terminals	IP 20	
Mechanical data		
Housing	housing for DIN rail mounting	
Dimensions	[mm]	75 x 55 x 110
Material	plastics	
Displays / operating elements		
Display	Switching status	2 x LED, red
Electrical connection		
Connection		