


Infrared temperature sensor

TW-008CODM30-QFPKG/US



- 1 LEDs switching status
2 7-segment LED display 2-digit
3 programming buttons



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2	
Measuring range	350...1350 °C	662...2462 °F

Application

Application	tempering temperatures; graphite; ceramics; metals; forging; sintering; heat treatment; rolling
-------------	--

Electrical data

Operating voltage [V]	10...34 DC
Current consumption [mA]	30; (24 V)
Protection class	III

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2
------------------------------	------------------------------

Inputs

Test input	test function active at U(test) > 9 V
------------	---------------------------------------

Outputs

Total number of outputs	2
Output signal	switching signal
Electrical design	PNP
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	150
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Wave length range [µm]	1...1.7
------------------------	---------



Infrared temperature sensor

TW-008CODM30-QFPKG/US

Measuring/setting range		
Measuring range	350...1350 °C	662...2462 °F
Factory setting	SP1 = 25 %; rP1 = 23 %; SP2 = 75 %; rP2 = 73 %	
Set point SP	350...1340 °C	662...2444 °F
Reset point rP	350...1340 °C	662...2444 °F
In steps of	10 °C	18 °F
Resolution		
Resolution of switching output	[K]	10
Resolution of display	[K]	10
Accuracy / deviations		
Accuracy	[K]	< ± 1 %; (of VMR (degree of emission = 1 and T = 23 °C))
Response times		
Response time	[ms]	2
Software / programming		
Adjustment of the switch point	programming buttons	
Parameter setting options	Hysteresis; normally open / normally closed; switch-on/switch-off delay	
Operating conditions		
Ambient temperature	[°C]	0...65
Storage temperature	[°C]	-20...80
Max. relative air humidity	[%]	95; (non condensing)
Protection	IP 65	
Tests / approvals		
EMC	DIN EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	DIN EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV coupling clamp
	DIN EN 61000-4-5 Surge	0,5 / 1 kV
	DIN EN 61000-4-6 HF conducted	10 V
	EN 55011 emission	class B
Shock resistance	DIN EN 60068-2-27	30 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[ANN]	117
Mechanical data		
Weight	[g]	374
Housing	threaded type	
Dimensions	[mm]	M30 x 1.5 / L = 163
Thread designation	M30 x 1.5	
Fibre optic connection	¼"-36UNS-2A	
Materials	threaded sleeve: stainless steel (1.4305 / 303); polyester	
Lens material	tempered optical glass	
Displays / operating elements		
Display	switching status	2 x LED, yellow
	function display	7-segment LED display, 2-digit
	measured values	7-segment LED display, 2-digit

TW7011



Infrared temperature sensor

TW-008CODM30-QFPKG/US

Operating elements	3	pushbuttons
--------------------	---	-------------

Аксессуары


Items supplied	lock nuts: 2
Accessories (optional)	fibre optics:, E35061 / E35062
	Measuring head:, E35060

Remarks

Remarks	MW = measured value
	MEW = Final value of the measuring range
Pack quantity	1 pcs.

Electrical connection

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
GY =	grey
WH =	white

Connector: 1 x M12