


Compact evaluation unit for speed monitoring

DIA3010-ZPKG/SS-000-K

Article to be discontinued

Alternative articles: DI5023 + E30436

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	10
Housing	Threaded type
Dimensions [mm]	M30 x 1.5 / L = 81

Application

Application	simple evaluation of rotating and linear movement with regard to underspeed; blocking
-------------	---

Electrical data

Nominal voltage DC [V]	10...36
Current consumption [mA]	< 15
Reverse polarity protection	yes

Outputs

Total number of outputs	1
Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Short-time current rating of switching output [mA]	250
Short-circuit proof	yes



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/SS-000-K

Overload protection	yes	
Monitoring range		
Sensing range	[mm]	10
Sensing range adjustable	no	
Measuring/setting range		
Setting range	[Imp/min]	5...300
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	10
Reaction times		
Start-up delay	[s]	15
Max. damping frequency	[Imp/min]	15000
Software / programming		
Adjustment of the switch point	multiturn potentiometer	
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 67	
Tests / approvals		
MTTF	[years]	898
Mechanical data		
Weight	[g]	200
Housing	Threaded type	
Mounting	flush mountable	
Dimensions	[mm]	M30 x 1.5 / L = 81
Thread designation	M30 x 1.5	
Material	brass special coating; PBT	
Tightening torque	[Nm]	50
Displays / operating elements		
Display	Switching status	1 x LED, green
Accessories		
Items supplied	valve plug type A.; DIN EN 175301-803	

DI5004


Compact evaluation unit for speed monitoring

DIA3010-ZPKG/SS-000-K



Electrical connection

Connection



Connector: 1 x SS connector