


DI5020



Compact evaluation unit for speed monitoring

DIA3010-ZPKG



1 potentiometer



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	10
Housing	Threaded type
Dimensions [mm]	M30 x 1.5 / L = 80

Application

Application	simple evaluation of rotating and linear movement with regard to underspeed; blocking
-------------	---

Electrical data

Nominal voltage DC [V]	10...36
Current consumption [mA]	< 20
Protection class	III
Reverse polarity protection	yes

Outputs

Total number of outputs	1
Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Short-time current rating of switching output [mA]	250
Short-circuit proof	yes
Overload protection	yes

Monitoring range

Sensing range [mm]	10
Sensing range adjustable	no
Operating distance [mm]	0...8.1

Measuring/setting range

Setting range [Imp/min]	5...3600
Measuring principle	inductive



Compact evaluation unit for speed monitoring

DIA3010-ZPKG

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	10
Reaction times		
Start-up delay		[s] 15
Max. damping frequency		[Imp/min] 18000
Software / programming		
Adjustment of the switch point		multiturn potentiometer
Operating conditions		
Ambient temperature		[°C] -25...80
Storage temperature		[°C] -25...80
Protection		IP 65; IP 67
Tests / approvals		
MTTF		[years] 656
Mechanical data		
Weight		[g] 282.3
Housing		Threaded type
Mounting		flush mountable
Dimensions		[mm] M30 x 1.5 / L = 80
Thread designation		M30 x 1.5
Material		brass special coating; PA; TPE-U
Tightening torque		[Nm] 50
Displays / operating elements		
Display		Switching status 1 x LED, green
Accessories		
Items supplied		lock nuts: 2

DI5020




Compact evaluation unit for speed monitoring

DIA3010-ZPKG

Electrical connection

Cable: 2 m, PUR; 3 x 0.5 mm²

Connection



BK = Core colors :
BN = black
BU = brown
blue