

DI601A




Compact evaluation unit for speed monitoring

DGA3012-WPKG/US/3D

Article no longer available - archive entry

Alternative articles: DI602A

When selecting an alternative article and accessories please note that technical data may differ!



- 1 LED 3 x
- 2 setting pushbutton



Product characteristics

Electrical design	PNP
Output function	normally open / closed; (configurable)
Sensing range [mm]	12
Dimensions [mm]	M18 x 1 / L = 68

Application

System	gold-plated contacts
Application	evaluation of rotating and linear movements with regard to underspeed; blocking

Electrical data

Nominal voltage DC [V]	10...36
Current consumption [mA]	< 15
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open / closed; (configurable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	150; (when used outside the hazardous area: 250; Pulse output: 15)
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

DI601A



Compact evaluation unit for speed monitoring

DGA3012-WPKG/US/3D

Monitoring range		
Sensing range	[mm]	12
Sensing range adjustable		no
Measuring/setting range		
Setting range	[Imp/min]	3...6000
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	10
Reaction times		
Start-up delay	[s]	0...15
Max. damping frequency	[Imp/min]	18000
Software / programming		
Adjustment of the switch point		Teach function
Operating conditions		
Ambient temperature	[°C]	-20...50
Note on ambient temperature		when used outside the hazardous area: -20...60 °C
Protection		IP 67
Tests / approvals		
ATEX marking		 II 3D Ex tD A22 IP67 T 80°C X ***)
EMC	EN 60947-5-2	
Mechanical data		
Weight	[g]	0.171
Mounting		non-flush mountable
Dimensions	[mm]	M18 x 1 / L = 68
Thread designation		M18 x 1
Material		stainless steel (1.4571/316Ti); PBT
Displays / operating elements		
Display	Switching status	1 x LED, yellow
	Power	1 x LED, green
Accessories		
Items supplied		impact protection housing
		lock nuts: 2
Electrical connection		
Connector: 1 x M12; coding: A; Contacts: gold-plated		
		


DI601A



Compact evaluation unit for speed monitoring

DGA3012-WPKG/US/3D

Connection



1: L+

2: Pulse output pulse sequence corresponds to damping frequency

3: L-

4: Switching output adjustable