




RFID read/write head with CAN interface and CANopen protocol

DTMHF IBRWCOUS03



Application		
Radio approval for	USA; Canada; EU/RED; Australia; Japan; China; Taiwan; India; Singapore; Ukraine; Brazil	
Note on radio approval	The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under “Downloads”.	
Electrical data		
Operating voltage	[V]	9...32 DC
Current consumption	[mA]	< 50 (24 V) / < 80 (12 V)
Protection class		III
Operating frequency	[MHz]	13,56
RFID standard		ISO 15693
Monitoring range		
Distance write/read head front	[mm]	120
Distance write/read head side	[mm]	60
Distance to the ID tag	[mm]	≤ 30
Interfaces		
Communication interface	CAN	
CAN		
Protocol	CANopen	
Operating conditions		
Ambient temperature	[°C]	-40...85
Storage temperature	[°C]	-40...85
Protection	IP 67; IP 69K	
Tests / approvals		
Shock resistance	EN 60068-2-27	40 g 6 ms / repetitive
	EN 60068-2-27	50 g 11 ms / not repetitive
Vibration resistance	EN 60068-2-6	20 g 10...2000 Hz
MTTF	[years]	477

DTM434



RFID read/write head with CAN interface and CANopen protocol

DTMHF IBRWCOUS03


Mechanical data		
Weight	[g]	198.5
Housing		Threaded type
Dimensions	[mm]	M30 x 1.5 / L = 70
Thread designation		M30 x 1.5
Material		housing: stainless steel; Protective cover: PPS; LED window: PEI

Displays / operating elements		
Display	Preoperational Mode	1 x LED, green lights
	Operational Mode	1 x LED, green flashing
	errors	1 x LED, red flashing
	tag communication	1 x LED, yellow lights

Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



1	not used
2	U+
3	GND
4	CAN_H
5	CAN_L