


DV1520



5-segment signal lamp

LED-Tower-5/Standard



CE cULus IO-Link

Application

Application

signaling machine conditions

Electrical data

Operating voltage	[V]	18...30 DC; (to SELV/PELV)
Nominal voltage DC	[V]	24
Current consumption	[mA]	< 200

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 6
------------------------------	-----------------------------

Inputs

Number of digital inputs		6
Input current High	[mA]	6

Interfaces

Communication interface	IO-Link
-------------------------	---------

DV1520



5-segment signal lamp

LED-Tower-5/Standard

Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
SIO mode	yes	
Required master port class	A	
Min. process cycle time [ms]	3.2	
Supported DeviceIDs	Type of operation	DeviceID
	default	850

Operating conditions		
Ambient temperature [°C]		-25...50
Storage temperature [°C]		-40...75
Max. relative air humidity [%]		90
Air pressure [kPa]		< 106
Max. height above sea level [m]		2000
Protection		IP 65

Mechanical data		
Weight [g]		519
Dimensions [mm]		Ø 70 / L = 244
Material		housing: ABS; lens: PC


Displays / operating elements		
Display	status	1 x LED, green
	LED segment	5 x 4 LED

Accessories		
Accessories (optional)		mounting base, E89060
		wall bracket, E89061
		Mounting adapter, E89063
		bracket with lateral cable entry, E89064
		mounting tube, E89065
		mounting tube, E89066
		mounting tube, E89067

Remarks		
Remarks	Further information is available in the manual.	
Pack quantity	1 pcs.	

Electrical connection - plug

Connector: M12; coding: A





5-segment signal lamp

LED-Tower-5/Standard

Connection

1	Digital input LED segment 5
2	not used
3	Digital input LED segment 3
4	Digital input LED segment 2
5	voltage supply
6	Digital input LED segment 1
7	Digital input LED segment 4
8	IO-Link (C/Q)

Diagrams and graphs

base mounting



DV1520

5-segment signal lamp

LED-Tower-5/Standard



wall mounting

