




Multifunction display for monitoring analog standard signals

DISPLAY/AX360

Article no longer available - archive entry

Alternative articles: DX2041
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Application		display of analog standard signals; e.g. pressure sensors, temperature sensors or flow sensors
Electrical data		
Frequency AC	[Hz]	50...60
Operating voltage tolerance	[%]	33...58
Operating voltage	[V]	230 / 115 AC / 24 DC
Current consumption	[mA]	110 (18 V); 90 (24 V); 80 (30 V)
Auxiliary energy for sensors DC	[V]	24; (±15 %, 150 mA; Short-circuit proof)
Inputs / outputs		
Number of inputs and outputs		Number of analog inputs: 2
Inputs		
Number of analog inputs		2
Outputs		
Analog current output	[mA]	4...20
Analog voltage output	[V]	0...10
Operating conditions		
Ambient temperature	[°C]	0...45



Multifunction display for monitoring analog standard signals

DISPLAY/AX360

Storage temperature	[°C]	-25...70
Protection		IP 65; (on the front)
Protection rating terminals		IP 20

Tests / approvals

EMC	EN 50081-1	
	EN 61000-6-2	

Mechanical data

Weight	[g]	552
Material		Noryl UL94-V-0

Displays / operating elements

Display	7-segment LED display, orange 6-digit 15 mm
---------	---

Electrical connection

screw terminals, DC: 10 x ...1.5 mm²

screw terminals, AC: 4 x ...2.5 mm²

Connection

