


Acceleration sensor

VIBRATION SENSOR



1 marking for X axis



Product characteristics

Measuring range of vibration	[g]	-40...40
Frequency range	[Hz]	1...4500
Measuring principle		capacitive

Application

Special feature	Drag chain suitability
-----------------	------------------------

Electrical data

Bias voltage DC	[V]	13...16
Operating current	[mA]	4...10
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Sensor type		microelectromechanical system (MEMS)

Measuring/setting range

Measuring range of vibration	[g]	-40...40
Frequency range	[Hz]	1...4500
Measuring principle		capacitive
Max. transverse sensitivity	[%]	5
Number of measurement axes		2

Accuracy / deviations

Measuring sensitivity		100 mV/g
Linearity deviation	[X21]	2

Operating conditions

Ambient temperature	[°C]	-30...85
Storage temperature	[°C]	-30...85
Protection		IP 67



Acceleration sensor

VIBRATION SENSOR

Tests / approvals		
EMC	EN IEC 61000-6-2	
	EN IEC 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g 11 ms
		500 g 1 ms
Vibration resistance	DIN EN 60068-2-6	20 g / 10...2000 Hz
MTTF	[ANN]	1233
UL approval	Ta	< 75 °C
	Enclosure type	Type 1
	подача напруги	Limited Voltage/Current
	File number UL	E251902
Mechanical data		
Weight	[g]	79.7
Type of mounting		M16 x 1,5
Materials		housing: stainless steel (1.4404 / 316L)
Tightening torque	[Nm]	8
Drag chain suitability		yes
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter
	bending radius for fixed installation	min. 4 x cable diameter
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 0.6 m, PUR, Ø 4.9 mm; 4 x 0.14 mm²		
Connector: 1 x M12; coding: A		
		
1 IEPE X 2 IEPE Z 3 GND 4 test		