


DX2051



Multifunction display for monitoring analog standard signals

DISPLAY/AX460/DC



panel cutout 91 x 43 mm



Product characteristics		
Dimensions	[mm]	48 x 112 x 116
Application		
Application	displaying and monitoring analog signals; e.g. pressure sensors, temperature sensors or flow sensors	
Electrical data		
Operating voltage	[V]	18...30 DC
Current consumption	[mA]	100
Inputs / outputs		
Number of inputs and outputs	Number of analog inputs: 2	
Inputs		
Number of analog inputs	2; (Spannungs- oder Stromeingang)	
Analog input (current)	[mA]	0...20
Analog input (voltage)	[V]	-10...10
Resolution of analog input	16 bit	
Precision analog input	[%]	0,1
Operating conditions		
Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...70
Protection	IP 65	
Protection rating terminals	IP 20	
Tests / approvals		
EMC	EN 61000-6-2	
	EN 61000-6-3	
	EN 61000-6-4	
Mechanical data		
Weight	[g]	300.5
Type of mounting	panel cutout: 91 x 43 mm	

DX2051



Multifunction display for monitoring analog standard signals

DISPLAY/AX460/DC	
Dimensions	[mm] 48 x 112 x 116
Material	Noryl UL94-V-0


Displays / operating elements

Display	Color display	full graphic LCD display, Touch screen
---------	---------------	--

Electrical connection

screw terminals:

Connection



NC not used