


E11566



T-splitter

T SPLITTER M12/2XUS



Application	
Design	for pressure sensors PNI
Application	Industrial applications
Electrical data	
Operating voltage [V]	< 30 AC / < 36 DC
Max. current load per module/slot [A]	3
Max. current load total [A]	3
Operating conditions	
Ambient temperature [°C]	-25...90
Protection	IP 68
Mechanical data	
Weight [g]	38.2
Material	housing: PUR
Remarks	
Remarks	orientation connectors A/B horizontal (for a vertical sensor)
Pack quantity	1 pcs.

E11566



T-splitter


T SPLITTER M12/2XUS

Electrical connection

Connection

AN_i_0711_GG

Original Scale Drawing (MTD)



↓ 32% ↑ 312,5%

EPS Source
Product Scale Drawing
Frame Size: 75 mm x 45 mm

