


E11847



Wiring block

ProcessLine SB V4A 25m



Electrical data		
Operating voltage	[V]	10...36 DC
Protection class		III
Max. current load per module/slot	[A]	4
Max. current load total	[A]	6
Outputs		
Electrical design		PNP
Operating conditions		
Ambient temperature	[°C]	-5...70



Wiring block

ProcessLine SB V4A 25m

Protection	IP 69K; (To ensure the protection rating unused sockets must be covered with the supplied protective caps.; Tightening torque: 1,3 Nm +/- 0,1 Nm)
------------	---

Tests / approvals

MTTF	[years]	2487
------	---------	------

Mechanical data

Weight	[g]	5376
Dimensions	[mm]	Ø 137.3 / L = 72
Material	threaded bush: stainless steel (1.4404 / 316L); LED-Fenster: PC; O-ring: EPDM; Protective cap: PP	
Molded-body material	stainless steel	
Number of ports splitter box	8	
Connector type	M12	

Displays / operating elements

Display	Switching status	16 x LED, yellow
	Power	1 x LED, green

Accessories

Items supplied	Protective caps: M12
----------------	----------------------

Remarks


Remarks	external voltage supply according to PELV
Pack quantity	1 pcs.

Electrical connection

Cable: 25 m, PUR / PVC, black, Ø 11 mm; 3 x 0.75 mm² + 16 x 0.34 mm²

Electrical connection - slot

Connector: 8 x M12; coding: A; Moulded body: stainless steel



E11847



Wiring block

ProcessLine SB V4A 25m

Connection



Core colors :

BK = black
 BN = brown
 BU = blue
 GN = green
 GY = grey
 PK = pink
 RD = red
 VT = lilac
 WH = white
 YE = yellow

E11847

Wiring block

ProcessLine SB V4A 25m

